# IFRM 12N1707

Inductive sensors special versions - high temperature

Article number: 10230318

#### Overview

- 4 mm
- NPN make function (NO)
- cable FEP, 1 m
- -25 ... 100 °C
- IP 67



Picture similar







Technical data	
General data	
Mounting type	Flush
Special type	High temperature
Nominal sensing distance Sn	4 mm
Hysteresis	3 20 % of Sr
Electrical data	
Switching frequency	< 2 kHz
Voltage supply range +Vs	6 30 VDC
Current consumption max. (no load)	12 mA
Output circuit	NPN make function (NO)
Voltage drop Vd	< 3 VDC

Electrical data	
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Туре	Cylindrical threaded
Housing material	Brass nickel plated
Dimension	12 mm
Housing length	40 mm
Connection types	Cable FEP, 1 m
Ambient conditions	
Operating temperature	-25 +100 °C
Protection class	IP 67

#### Remarks

With integral electronics of up to +100 °C




# IFRM 12N1707

Inductive sensors special versions - high temperature

Article number: 10230318

### **Dimension drawing**



## Connection diagram

