


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer), recalibrated 28.08.2017. The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronik GmbH.



Vendor	Baumer
Model	LXG-20C.P
Serial number	1057600417
Sensor diagonal	12.75 mm
Lens category	C-Mount
Resolution	2048 × 1088, 8 bit
Pixel size	5.50 μm × 5.50 μm
Sensor	CMOSIS CMV2000
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	465.2 nm
Wavelength FWHM	20.8 nm
Gain / BlackLevel	1.0 / 3.0
Operation point 2	
Wavelength centroid	535.8 nm
Wavelength FWHM	31.9 nm
Gain / BlackLevel	1.0 / 3.0
Operation point 3	
Wavelength centroid	630.8 nm
Wavelength FWHM	13.3 nm
Gain / BlackLevel	1.0 / 3.0
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 3.0
Exposure control	By irradiance	Environmental temperature	23.6°C
Exposure time	414.00 μ s	Camera body temperature	35.7°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerGB8	Wavelength, centr., FWHM	465 nm, 20.8 nm



Quantum efficiency

 η 44.1%

Overall system gain

 K 0.024 DN/e⁻
 $1/K$ 41.645 e⁻/DN

Temporal dark noise & DSNU

 $\sigma_{y,\text{dark}}$ 0.48 DN¹

DSNU₁₂₈₈ 0.49 DN

 σ_d 16.08 e⁻

DSNU₁₂₈₈ 20.44 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 99

39.9 dB

6.6 bit

 $1/\text{SNR}_{\text{max}}$ 1.01 %

PRNU₁₂₈₈ 1.56 %

Nonlinearity

LE 0.41%

LE_{min} -0.46%

LE_{max} 0.36%

Sensitivity & saturation

 $\mu_{p,\text{min}}$ 46.7 p¹

1.54 p/ μm^2
 $\mu_{p,\text{sat}}$ 22317 p

738 p/ μm^2
 $\mu_{e,\text{min}}$ 20.6 e⁻

0.68 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 9844 e⁻

325 e⁻/ μm^2

Dynamic range

DR 478¹

53.6 dB¹

8.9 bit¹

Dark current

 $\mu_{c,\text{mean}}$ 10.8 DN/s



 $\mu_{c,\text{mean}}$ 447.9 e⁻/s

 $\mu_{c,\text{var}}$ 245.2 e⁻/s

¹Dark noise too low, estimate not reliable, all dark noise related parameters not reliable

EMVA 1288 Summary Sheet for Operating Point 2

Type of data	Single	Gain / BlackLevel	1.0 / 3.0
Exposure control	By irradiance	Environmental temperature	23.6°C
Exposure time	414.00 μ s	Camera body temperature	35.7°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerGB8	Wavelength, centr., FWHM	536 nm, 31.9 nm



Quantum efficiency

 η 44.5%

Overall system gain

 K 0.024 DN/e⁻
 $1/K$ 42.416 e⁻/DN

Temporal dark noise & DSNU

 $\sigma_{y,\text{dark}}$ 0.48 DN¹

DSNU₁₂₈₈ 0.50 DN

 σ_d 16.49 e⁻

DSNU₁₂₈₈ 21.03 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 102

40.1 dB

6.7 bit

 $1/\text{SNR}_{\text{max}}$ 0.99 %

PRNU₁₂₈₈ 1.33 %

Nonlinearity

LE 0.63%

LE_{min} -0.79%

LE_{max} 0.46%

Sensitivity & saturation

 $\mu_{p,\text{min}}$ 47.3 p¹

1.56 p/ μ m²¹
 $\mu_{p,\text{sat}}$ 23135 p

765 p/ μ m²
 $\mu_{e,\text{min}}$ 21.0 e⁻

0.70 e⁻/ μ m²
 $\mu_{e,\text{sat}}$ 10304 e⁻

341 e⁻/ μ m²

Dynamic range

DR 490¹

53.8 dB¹

8.9 bit¹

Dark current

 $\mu_{c,\text{mean}}$ 10.8 DN/s



 $\mu_{c,\text{mean}}$ 456.6 e⁻/s

 $\mu_{c,\text{var}}$ 253.3 e⁻/s

¹Dark noise too low, estimate not reliable, all dark noise related parameters not reliable

EMVA 1288 Summary Sheet for Operating Point 3

Type of data	Single	Gain / BlackLevel	1.0 / 3.0
Exposure control	By irradiance	Environmental temperature	23.6°C
Exposure time	414.00 μ s	Camera body temperature	35.7°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerGB8	Wavelength, centr., FWHM	631 nm, 13.3 nm



Quantum efficiency

 η 44.7%

Overall system gain

 K 0.023 DN/e⁻
 $1/K$ 42.633 e⁻/DN

Temporal dark noise & DSNU

 $\sigma_{y,\text{dark}}$ 0.48 DN¹

DSNU₁₂₈₈ 0.48 DN

 σ_d 16.23 e⁻

DSNU₁₂₈₈ 20.30 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 102

40.2 dB

6.7 bit

 $1/\text{SNR}_{\text{max}}$ 0.98 %

PRNU₁₂₈₈ 1.24 %

Nonlinearity

LE 0.73%

LE_{min} -0.87%

LE_{max} 0.58%

Sensitivity & saturation

 $\mu_{p,\text{min}}$ 46.6 p¹

1.54 p/ μ m²¹
 $\mu_{p,\text{sat}}$ 23188 p

767 p/ μ m²
 $\mu_{e,\text{min}}$ 20.9 e⁻

0.69 e⁻/ μ m²
 $\mu_{e,\text{sat}}$ 10376 e⁻

343 e⁻/ μ m²

Dynamic range

DR 497¹

53.9 dB¹

9.0 bit¹

Dark current

 $\mu_{c,\text{mean}}$ 10.8 DN/s

 $\mu_{c,\text{mean}}$ 458.9 e⁻/s

 $\mu_{c,\text{var}}$ 257.5 e⁻/s

¹Dark noise too low, estimate not reliable, all dark noise related parameters not reliable