Spring washer coupling (D1=6 / D2=16)

For encoder with solid shaft Article number: 11034139


Overview

- Backlash-free and angle-synchronous transmission of rotary movements
- Plug-in version
- Electric isolated
- Suitable for very high speeds
- Good compensation of all misalignments



Technical data			
Technical data		Technical data	
Shaft diameter D1	6 mm	Maximum torque	60 Ncm
Shaft diameter D2	16 mm	Admissible axial movement	± 0.4 mm
Operating speed	≤12000 rpm	Admissible parallel misalignment	± 0.3 mm
Operating temperature	-10+80 °C		
Moment of inertia	35 gcm²	Admissible angular error	± 2.5 °
Torsional rigidity	30 Nm/rad	Weight approx.	30 g
Radial spring stiffness	40 N/mm	Material	Clamping ring: aluminium Spring washer: plastic


Dimensions



Spring washer coupling (D1=6 / D2=16)

For encoder with solid shaft Article number: 11034139

Assembly drawing



a = Admissible axial movementb = Admissible parallel misalignmentc = Admissible angular error