

Overview

- 50 ... 350 mm
- pulsed red laser diode
- analog
- Teach-in: button / external
- connector M8 4 pin
- 50 °C
- IP 67



Picture similar



Technical data

General data

Measuring distance Sd	50 ... 350 mm
Adjustment	Teach-in: button / external
Teach-in range min.	> 5 mm
Power on indication	LED green
Soiled lens indicator	LED red
Resolution	10 ... 400 µm
Linearity error	± 0.05 ... 1.2 mm
Beam type	Line
Beam width	2 mm
Beam height	4 ... 9 mm
Interference suppression	< 30 ms
Temperature drift	< 0,04 % Sde/K

Light Source

Light source	Pulsed red laser diode
Wave length	650 nm
Laser class	2

Electrical data

Response time / release time	< 0.9 ms
------------------------------	----------

Electrical data

Voltage supply range +Vs	12 ... 28 VDC
Current consumption max. (no load)	80 mA
Output circuit	Analog
Output signal	0 ... 10 VDC
Load resistance	> 100 kOhm
Short circuit protection	Yes
Reverse polarity protection	Yes, Vs to GND

Mechanical data

Width / diameter	13.4 mm
Height / length	48.2 mm
Depth	40 mm
Type	Rectangular
Housing material	Aluminum
Front (optics)	Glass
Connection types	Connector M8 4 pin

Ambient conditions


Ambient light immunity	< 30 kLux
Protection class	IP 67
Operating temperature	0 ... +50 °C

OADM 13U6575/S35A

Distance sensors - miniature


Article number: 10159644

Dimension drawing




* emitter axis


Laser warning



Connection diagram



Resolution



Linearity error

