

## Overview

- 30 ... 70 mm
- pulsed red laser diode
- analog
- Teach-in: button / external
- connector M12 5 pin, rotatable
- 50 °C
- IP 67



Picture similar



## Technical data

### General data

Measuring distance Sd	30 ... 70 mm
Beam diameter	1 ... 0.2 mm
Adjustment	Teach-in: button / external
Teach-in range min.	> 2 mm
Power on indication	LED green
Soiled lens indicator	LED red
Resolution	4 ... 20 µm
Linearity error	± 0.012 ... 0.06 mm
Beam type	Point

### Light Source

Light source	Pulsed red laser diode
Wave length	650 nm
Laser class	2

### Electrical data

Response time / release time	< 0.9 ms
Voltage supply range +Vs	12 ... 28 VDC

### Electrical data

Current consumption max. (no load)	100 mA
Output circuit	Analog
Output signal	4 ... 20 mA
Load resistance (analog I)	< (+Vs - 6 V) / 0,02 A
Short circuit protection	Yes
Reverse polarity protection	Yes, Vs to GND


### Mechanical data

Width / diameter	20.6 mm
Height / length	65 mm
Depth	50 mm
Type	Rectangular
Housing material	Die-cast zinc
Front (optics)	Glass
Connection types	Connector M12 5 pin, rotatable

### Ambient conditions


Protection class	IP 67
Operating temperature	0 ... +50 °C

## Dimension drawing



- \* emitter axis


## Laser warning



## Connection diagram



## Resolution



## Linearity error

