O300H.ER-GW1B.PVNV

Through beam sensors - hygiene Article number: 11167294

Overview

- receiver
- through beam sensor
- 10 m
- push-pull
- Teach-in: remote
- flylead connector M8, L=200 mm
- -25 ... 60 °C
- IP 68/69K & proTect+



Picture similar







Technical data	
General data	
Туре	Through beam sensor
Special type	Hygienic design
Emitter / receiver	Receiver
Actual range Sb	10 m
Nominal range Sn	15 m
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Power on indication	LED green
Sensitivity adjustment	Teach-in: remote
Alignment optical axis	< 2°
Approvals/certificates	Ecolab Adapted from EHEDG
Electrical data	
Response time / release time	< 0.49 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	40 mA

Current consumption typ.	30 mA
Voltage drop Vd	< 3 VDC
Output function	Light / dark operate
Output circuit	Push-pull
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	16.5 mm
Height / length	34.6 mm
Depth	28.7 mm
Depth Type	28.7 mm Rectangular
•	
Туре	Rectangular
Type Housing material	Rectangular Stainless steel 1.4404 (V4A)
Type Housing material Front (optics)	Rectangular Stainless steel 1.4404 (V4A) PMMA
Type Housing material Front (optics) Connection types	Rectangular Stainless steel 1.4404 (V4A) PMMA

Remarks


Magnetic Teach

Electrical data


O300H.ER-GW1B.PVNV

Through beam sensors - hygiene Article number: 11167294


Technical drawings



Connection diagram



Pin assignment



Excess gain curve

