

Overview

- 50 ... 400 mm
- pulsed point source LED
- analog
- IO-Link
- connector M8 4 pin
- 50 °C
- IP 67



Picture similar



Technical data

General data

Measuring distance Sd	50 ... 400 mm
Beam diameter	8 mm
Adjustment	IO-Link
Teach-in range min.	> 20 mm
Power on indication	LED green
Soiled lens indicator	LED red
Resolution	100 ... 1000 µm
Linearity error	± 1.5 ... 4 mm
Beam type	Point
Temperature drift	< 0,1 % Sde/K

Light Source

Light source	Pulsed point source LED
Wave length	660 nm

Electrical data

Response time / release time	< 3 ms
Voltage supply range +Vs	14 ... 26 VDC
Current consumption max. (no load)	80 mA
Output circuit	Analog

Electrical data

Output signal	0 ... 10 VDC
Load resistance (analog U)	> 100 kOhm
Output current	< 100 mA
Alarm output	Push-pull
Short circuit protection	Yes
Reverse polarity protection	Yes, Vs to GND

Communication interface

Interface	IO-Link V1.1
-----------	--------------

Mechanical data

Width / diameter	14.8 mm
Height / length	43 mm
Depth	31 mm
Type	Rectangular
Housing material	Plastic (ASA, MABS)
Front (optics)	PMMA
Connection types	Connector M8 4 pin


Ambient conditions

Protection class	IP 67
Operating temperature	0 ... +50 °C

Remarks


- IO-Link: Measuring range limit, average determination, service status, alarm output, switching window

Dimension drawing




- * emitter axis

Connection diagram



Linearity error



Resolution

