

# O300.ZL-NV1T.72N

Diffuse sensors with intensity difference

Article number: 11181087

### Overview

- intensity difference
- 10 ... 250 mm
- pulsed red laser diode
- NPN complementary
- connector M8 4 pin
- -10 ... 60 °C
- IP 67



25 mA

< 2.5 VDC

Light / dark operate

Picture similar





Technical data	
General data	
Туре	Intensity difference
Light source	Pulsed red laser diode
Sensing distance Tw	10 250 mm
Repeat accuracy	< 0.1 mm at laser focus
Power on indication	LED green
Light indicator	LED yellow
Sensing distance adjust- ment	qTeach
Laser class	1
Distance to focus	80 mm
Wave length	656 nm
Suppression of reciprocal influence	Yes
Alignment optical axis	< 2°
Electrical data	
Response time / release time	< 0.1 ms
Voltage supply range +Vs	11 30 VDC
Current consumption max. (no load)	30 mA

Output circuit	NPN complementary
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	12.9 mm
Height / length	32.3 mm
Depth	23 mm
Туре	Rectangular
Housing material	Plastic (ASA, PMMA)
Front (optics)	PMMA
Connection types	Connector M8 4 pin
Ambient conditions	
Protection class	IP 67
Operating temperature	-10 +60 °C

Electrical data

Voltage drop Vd

Output function

Current consumption typ.

## Remarks


qTeach

# O300.ZL-NV1T.72N

Diffuse sensors with intensity difference

Article number: 11181087

### **Dimension drawing**




### Laser warning

# CLASS 1 LASER PRODUCT

IEC 60825-1/2014
Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019


## **Connection diagram**



# Pin assignment



### Beam characteristic (typically)



## Relative receiving signal

