O500.ER-NV1T.72CU

Through beam sensors - for longer ranges

Article number: 11167281

Overview

- receiver
- through beam sensor
- 25 m
- NPN complementary
- qTeach
- cable 4 pin, 2 m
- -25 ... 60 °C
- IP 67



Picture similar





Technical data	
General data	
Туре	Through beam sensor
Emitter / receiver	Receiver
Actual range Sb	25 m
Nominal range Sn	40 m
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Power on indication	LED green
Sensitivity adjustment	qTeach
Alignment optical axis	< 1°
Electrical data	
Response time / release time	< 0.49 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	40 mA
Current consumption typ.	30 mA

Electrical data	
Voltage drop Vd	< 3 VDC
Output function	Light / dark operate
Output circuit	NPN complementary
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	18 mm
Height / length	45 mm
Depth	32 mm
Туре	Rectangular
Housing material	Plastic (ASA, PMMA)
Front (optics)	PMMA
Connection types	Cable 4 pin, 2 m
Ambient conditions	
Operating temperature	-25 +60 °C
Protection class	IP 67

Remarks


qTeach

O500.ER-NV1T.72CU

Through beam sensors - for longer ranges

Article number: 11167281

Technical drawings



Connection diagram

