

FZAM 18N6460/S14

Diffuse sensors with intensity difference Article number: 10128875

Overview

- intensity difference
- 60 ... 430 mm
- pulsed infrared diode
- NPN
- Teach-in
- connector M12 4 pin
- -25 ... 55 °C
- IP 67



Picture similar





Technical data	
General data	
Туре	Intensity difference
Light source	Pulsed infrared diode
Sensing distance Tw	60 430 mm
Sensing distance Tw (with doubling lense)	80 800 mm
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED green
Output indicator	LED yellow
Sensitivity adjustment	Teach-in
Wave length	880 nm
Suppression of reciprocal influence	Yes
Electrical data	
Response time / release time	< 1 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	55 mA


Electrical data	
Current consumption typ.	40 mA
Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate, alarm
Output circuit	NPN
Output current	< 200 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	18 mm
Height / length	60 mm
Туре	Cylindrical threaded
Housing material	Brass nickel plated / PC
Front (optics)	PC
Connection types	Connector M12 4 pin
Ambient conditions	
Protection class	IP 67
Operating temperature	-25 +55 °C



FZAM 18N6460/S14

Diffuse sensors with intensity difference Article number: 10128875

Dimension drawing



Connection diagram

