Subject to modification in technic and design. Errors and omissions excepte

Absolute encoders - bus interfaces

Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP



PMG10 - picture similar

Features

- Magnetic sensing method
- Function display via LEDs
- Multiturn sensing with Energy Harvesting technology, without gear or battery
- Two-sided bearing system with hybrid bearings
- Special protection against corrosion C5-M

Optional

- Integrated speed switch
- Additional output incremental with zero pulse

Technical data - electrical ratings		
Voltage supply	1030 VDC	
Short-circuit proof	Yes	
Consumption w/o load	≤200 mA	
Initializing time	≤500 ms after power on	
Interface	Profibus-DPV0/V2	
Function	Multiturn	
Transmission rate	9.612000 kBaud	
Device adress	Rotary switches in bus connecting box	
Steps per revolution	8192 / 13 bit	
Number of revolutions	65536 / 16 bit	
Additional outputs	Square-wave TTL/HTL,TTL/ RS422	
Sensing method	Magnetic	
Interference immunity	EN 61000-6-2	
Emitted interference	EN 61000-6-3	
Programmable parameters	Steps per revolution Number of revolutions Preset, scaling, rotating direction	
Diagnostic function	Position or parameter error	
Status indicator	DUO-LED (bus connecting box) 4 LEDs in device back side	
Approval	CE	

Technical data - electrical ratings (speed switches)			
Switching accuracy ±2 % (or 1 Digit)			
Switching outputs	1 output (Open collector, solid state relay on request)		
Output switching capacity	30 VDC; ≤100 mA		
Switching delay time	≤20 ms		


Technical data - mechanical design		
Size (flange)	ø115 mm	
Shaft type	ø11 mm solid shaft	
Flange	EURO flange B10 Housing foot B3	
Protection DIN EN 60529	IP 66/IP 67	
Operating speed	≤6000 rpm	
Range of switching speed	ns (off) = ±26000 rpm, factory setting 6000 rpm	
Operating torque typ.	10 Ncm	
Rotor moment of inertia	1 kgcm²	
Admitted shaft load	≤450 N axial ≤650 N radial	
Materials	Housing: aluminium alloy Shaft: stainless steel	
Corrosion protection	IEC 60068-2-52 Salt mist for ambient conditions C5-M (CX) according to ISO 12944-2	
Operating temperature	-40+85 °C	
Relative humidity	95 % non-condensing	
Resistance	IEC 60068-2-6 Vibration 30 g, 10-2000 Hz IEC 60068-2-27 Shock 400 g, 1 ms	
Weight approx.	2.7 kg (depending on version)	
Connection	Bus connecting box Terminal box incremental	

Subject to modification in technic and design. Errors and omissions excepted

Absolute encoders - bus interfaces

Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP



- (Standard: Open collector, solid state relay on request)
- * Only for connection with 1x bus connecting + 1x terminal box (F or G)
- ** Please specify the exact switching speed in addition to the part number (factory setting).



Absolute encoders - bus interfaces

Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP

Part number - tables	Accessories		
Additional output*		Mounting accessories	
0 (Without) Q (8192 ppr TTL/HTL (Vin=Vout), 6 channels, electrically isolated) P (8192 ppr TTL/RS422, 6 channels)		Spring washer coupling for solid shaft ø612 mm	
		Spring washer coupling for solid shaft ø1116 mm	
G (5000 ppr TTL/HTL (Vin=Vout), 6 channels, electrically isolated)	K 60	Spring washer coupling for solid shaft ø1122 mm	

isolate	ed)
Н	(5000 ppr TTL/RS422, 6 channels)
K	(4096 ppr TTL/HTL (Vin=Vout), 6 channels, electrically
isolate	ed)
J	(4096 ppr TTL/RS422, 6 channels)
7	(3072 ppr TTL/HTL (Vin=Vout), 6 channels, electrically
isolate	ed)

- 8 (3072 ppr TTL/RS422, 6 channels) 9 (2048 ppr TTL/HTL (Vin=Vout), 6 channels, electrically isolated)
 - 4 (2048 ppr TTL/RS422, 6 channels)
- 5 (1024 ppr TTL/HTL (Vin=Vout), 6 channels, electrically
 - 6 (1024 ppr TTL/RS422, 6 channels)
- 1 (512 ppr TTL/HTL (Vin=Vout), 6 channels, electrically
 - 2 (512 ppr TTL/RS422, 6 channels)


Absolute encoders - bus interfaces

Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP


Profibus-DP V0 - Terminal assignment

View A 1) - View inside bus connecting box



View A¹ 1) - View into connector "Voltage supply"

male	Connection	Description
1	UB	Voltage supply 1030 VDC
3	GND	Ground connection for UB




Connector M12 (male) 4-pin, A-coded


View A^{2 1)} and A^{3 1)} - View into connector "Data transmission"

male /		
female	Connection	Description

		•
2	Α	Negative serial data transmission
4	В	Positive serial data transmission







Connector M12 (female, **A**³ 1)) 5-pin, B-coded

Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections UB-UB and GND-GND is 1 A each.

Profibus-DP V0 - Features		
Bus protocol	Profibus-DP V0	
Profibus-Features	Device Class 1 and 2	
Data Exch. functions	Input: Position value Output: Preset value	
Preset value	The "Preset" parameter can be used to set the encoder to a predefined value that corresponds to a specific axis position of the system.	
Parameter functions	Rotating direction: The relationship between the rotating direction and rising or falling output code values can be set in the operating parameter. Scaling: The parameter values set the number of steps per turn and the overall resolution.	
Diagnostic	The encoder supports the following error messages: - Position error	
Factory setting	User address 00	

Profibus-DP V0 - Termination



both ON = final user both OFF = user xx

Profibus-DP V0 - User address





Defined by rotary switch. Example: User address 23


¹⁾ See dimensions



PMG10 - Profibus DP


Profibus-DP V2 - Terminal assignment

View A 1) - View inside bus connecting box



View A¹ 1) - View into connector "Voltage supply"

m	nale	Connection	Description
	1	UB	Voltage supply 1030 VDC
	3	GND	Ground connection for UB




Connector M12 (male) 4-pin, A-coded


View A^{2 1)} and A^{3 1)} - View into connector "Data transmission"

male /		
female	Connection	Description

		•
2	Α	Negative serial data transmission
4	В	Positive serial data transmission







Connector M12 (female, **A**³ 1)) 5-pin, B-coded

Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections UB-UB and GND-GND is 1 A each.

Profibus-DP V2 - Features	
Bus protocol	Profibus-DP V2
Profibus-Features	Device Class 3 and 4
Data Exch. functions	Input: Position value Output: Preset value
Preset value	The "Preset" parameter can be used to set the encoder to a predefined value that corresponds to a specific axis position of the system.
Parameter functions	Rotating direction: The relationship between the rotating direction and rising or falling output code values can be set in the operating parameter. Scaling: The parameter values set the number of steps per turn and the overall resolution.
Diagnostic	The encoder supports the following error messages: - Position error

User address 00

Profibus-DP V2 - Termination



Factory setting

both ON = final user both OFF = user xx

Profibus-DP V2 - User address





Defined by rotary switch. Example: User address 23

9 Subject to modification in technic and design. Errors and omissions excepted.

Absolute encoders - bus interfaces


Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP

Speed switch / additional output incremental - Terminal significance

Ub ²⁾	Voltage supply
0V ²⁾	Ground
A+ 2)	Output signal channel 1
A-2)	Output signal channel 1 inverted
B+ ²⁾	Output signal channel 2 (offset by 90° to channel 1)
B-2)	Output signal channel 2 inverted
R+ 2)	Zero pulse (reference signal)
R-2)	Zero pulse inverted
nE+	System OK+ / error output
nE-	System OK- / error output inverted
SP+ 3)	DSL_OUT1 / speed switch
	(Open collector, solid state relay on
	request)
SP-3)	DSL_OUT2 / speed switch
	(0V, solid state relay on request)
dnu	Do not use

Speed switch / additional output incremental - Terminal assignment terminal box



Additional output incremental - Trigger level

Trigger level	TTL/RS422
High / Low	≥2.5 V / ≤0.5 V
Transmission length	≤550 m @ 100 kHz
Output frequency	≤600 kHz
Trigger level	TTL/HTL (Vin = Vout)
High / Low	≥2.5 V / ≤0.5 V (TTL)
	≥Ub -3 V / ≤1.5 V (HTL)
Transmission length	≤550 m @ 100 kHz (TTL)
	≤350 m @ 100 kHz (HTL)
Output frequency	≤600 kHz (TTL); ≤350 kHz (HTL)


Electrically isolated:

The output TTL/HTL (Vin = Vout) at the additional output incremental is electrically isolated and requires a separate power supply.


- 1) See dimensions
- ²⁾ Additional output incremental (option)
- 3) Speed switch (option)

Additional output incremental - Output signals

Version with additional output incremental at positive rotating direction ¹⁾



Speed switch - Switching characteristics



n = Speed

+ns (off) = Switch-off speed at shaft rotation in positive rotating direction ¹⁾.

-ns (off) = Switch-off speed at shaft rotation in negative rotating direction ¹⁾.

Switching hysteresis *□*:

5...100 % (factory setting = 10 % min. 1 Digit)

+ns (on) = Switch-on speed at shaft rotation in positive rotating direction ¹⁾.

-ns (on) = Switch-on speed at shaft rotation in negative rotating direction ¹⁾.



Subject to modification in technic and design. Errors and omissions excepted.


Absolute encoders - bus interfaces

Solid shaft ø11 mm with EURO flange B10 or housing foot B3 Profibus DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

PMG10 - Profibus DP

Dimensions

Version with EURO flange B10



Version with housing foot B3

