

FVDK 22P6501/S14C

Fiber optic sensors & cables

Article number: 10119655

Overview

- pulsed red LED
- PNP
- Teach-in
- connector M12 5 pin
- -25 ... 55 °C
- IP 65



Picture similar



Technical data

General data

Version	Integrated alarm output
Actual range Sb (FSE 200C1002)	320 mm
Sensing distance Tw (FUE 200C1003)	90 mm
Light source	Pulsed red LED
Light indicator	LED green
Alignment / soiled lens in- dicator	LED green, flashing
Output indicator	LED yellow
Adjustment	Teach-in
Wave length	660 nm
Suppression of reciprocal influence	Yes

Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	68 mA

Electrical data

Current consumption typ.	50 mA
Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate switchable
Min. output pulse length	40 ms
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Width / diameter	22 mm
Height / length	33.2 mm
Depth	60 mm
Type	Rectangular
Housing material	PBT / PC
Connection types	Connector M12 5 pin

Ambient conditions


Operating temperature	-25 ... +55 °C
Protection class	IP 65

FVDK 22P6501/S14C

Fiber optic sensors & cables

Article number: 10119655

Dimension drawing



Connection diagram

