O500H.ER-GW1B.PVOV

Through beam sensors - hygiene Article number: 11167299

Overview

- receiver
- through beam sensor
- 25 m
- push-pull
- Teach-in: remote
- flylead connector M12, L=200 mm
- -25 ... 60 °C
- IP 68/69K & proTect+



Picture similar







Technical data	
General data	
Туре	Through beam sensor
Special type	Hygienic design
Emitter / receiver	Receiver
Actual range Sb	25 m
Nominal range Sn	40 m
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Power on indication	LED green
Sensitivity adjustment	Teach-in: remote
Alignment optical axis	< 1°
Approvals/certificates	Ecolab Adapted from EHEDG
Electrical data	
Response time / release time	< 0.49 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	40 mA


4	
tor	
)G	

Da	-	wle o
ĸe	IIIa	ırks
•••	••••	


Magnetic Teach

Electrical data	
Current consumption typ.	30 mA
Voltage drop Vd	< 3 VDC
Output function	Light / dark operate
Output circuit	Push-pull
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	20.2 mm
Height / length	47.7 mm
Depth	36.4 mm
Туре	Rectangular
Housing material	Stainless steel 1.4404 (V4A)
Front (optics)	PMMA
Connection types	Flylead connector M12, L=200 mm
Ambient conditions	
Operating temperature	-25 +60 °C
Protection class	IP 68/69K & proTect+

Technical drawings



Connection diagram



Pin assignment

