# O500H.TR-ZZZZ.PVOV

Through beam sensors - hygiene Article number: 11167296

#### Overview

- emitter
- through beam sensor
- 25 m
- pulsed red LED
- flylead connector M12, L=200 mm
- -25 ... 60 °C
- IP 68/69K & proTect+



Picture similar








| Technical data               |                           |
|------------------------------|---------------------------|
| General data                 |                           |
| Туре                         | Through beam sensor       |
| Special type                 | Hygienic design           |
| Emitter / receiver           | Emitter                   |
| Light source                 | Pulsed red LED            |
| Actual range Sb              | 25 m                      |
| Nominal range Sn             | 40 m                      |
| Power on indication          | LED green                 |
| Wave length                  | 645 nm                    |
| Alignment optical axis       | < 1°                      |
| Approvals/certificates       | Ecolab Adapted from EHEDG |
| Electrical data              |                           |
| Response time / release time | < 0.49 ms                 |
| Voltage supply range +Vs     | 10 30 VDC                 |

| Electrical data                    |                                 |
|------------------------------------|---------------------------------|
| Current consumption max. (no load) | 40 mA                           |
| Current consumption typ.           | 30 mA                           |
| Reverse polarity protection        | Yes                             |
| Mechanical data                    |                                 |
| Width / diameter                   | 20.2 mm                         |
| Height / length                    | 47.7 mm                         |
| Depth                              | 36.4 mm                         |
| Туре                               | Rectangular                     |
| Housing material                   | Stainless steel 1.4404 (V4A)    |
| Front (optics)                     | PMMA                            |
| Connection types                   | Flylead connector M12, L=200 mm |
| Ambient conditions                 |                                 |
| Operating temperature              | -25 +60 °C                      |
| Protection class                   | IP 68/69K & proTect+            |

### Remarks

Magnetic Teach


# **Technical drawings**



# **Connection diagram**



# Pin assignment



# Beam characteristic (typically)

