

Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

Overview

- Magnetic sensing method
- Function display via LEDs
- Multiturn sensing with Energy Harvesting technology "MicroGen", without gear or battery
- Two-sided bearing system with hybrid bearings
- Special protection against corrosion CX (C5-M)



Picture similar

HUBNER
BERLIN
A Raymor Brand

microGen Energy Harvesting

Technical data	
Technical data - electrical r	atings
Voltage supply	1030 VDC
Short-circuit proof	Yes
Consumption w/o load	≤200 mA
Initializing time	≤ 500 ms after power on
Interface	Profibus-DPV0/V2
Function	Multiturn
Transmission rate	9.6 12000 kBaud
Device adress	Rotary switches in bus connecting box
Steps per revolution	8192 / 13 bit
Number of revolutions	65536 / 16 bit
Additional outputs	Square-wave TTL/HTL,TTL/RS422
Sensing method	Magnetic
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Programmable parameters	Steps per revolution Number of revolutions Preset, scaling, rotating direction
Diagnostic function	Position or parameter error
Status indicator	DUO-LED (bus connecting box) 4 LEDs in device back side
Approval	CE UL approval / E217823 EAC
Technical data - electrical r	atings (speed switch)
Switching accuracy	± 2 % (or 1 Digit)
Switching outputs	1 output (Open collector, solid state relay on request)

Technical data - electrical ra	atings (speed switch)
Output switching capacity	30 VDC; ≤100 mA
Switching delay time	≤20 ms
Technical data - mechanica	l design
Size (flange)	ø105 mm
Shaft type	ø1620 mm (through hollow shaft)
Flange	Support plate, 360° freely positionable
Protection EN 60529	IP 66/IP 67
Operating speed	≤6000 rpm
Range of switching speed	ns (off) = ±26000 rpm
Operating torque typ.	10 Ncm
Rotor moment of inertia	950 gcm²
Admitted shaft load	≤450 N axial ≤650 N radial
Material	Housing: aluminium alloy Shaft: stainless steel
Corrosion protection	IEC 60068-2-52 Salt mist for ambient conditions CX (C5-M) accord- ing to ISO 12944-2
Operating temperature	-40+85 °C
Relative humidity	95 % non-condensing
Resistance	IEC 60068-2-6 Vibration 30 g, 10-2000 Hz IEC 60068-2-27 Shock 400 g, 1 ms
Weight approx.	2.2 kg (depending on version)
Connection	Bus connecting box Terminal box incremental

Optional


- Integrated speed switch
- Additional output incremental with zero pulse

Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

Terminal assignment

Profibus-DP - View A (see dimension) View inside bus connecting box Profibus



Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections UB-UB and GND-GND is 1 A each.

Terminating resistor (1)

ON = Last user OFF = User x



User address (2)


Defined by rotary switch. Example: User address 23





View A1 (see dimension)

View into connector bus "voltage supply"



Connector M12 (male)


4-pin, A-coded


Pin	Connection	
1	UB	
2	dnu	
3	GND	
4	dnu	

Terminal assignment

View A2 and A3 (see dimension)

View into connector bus "data transmission"





Connector M12 (male, **A2**) 5-pin, B-coded

Connector M12 (female, **A3**) 5-pin, B-coded

Pin	Connection
2	A
4	В


View B (see dimension)

Connecting terminal terminal box

Speed switch /

additional output II (HTL, TTL)

* Assignment depends on encoder version



Terminal significance

Profibus

Connection	Description
GND	Ground for UB
UB	Voltage supply 1030 VDC
A	Negative serial data transmission
В	Positive serial data transmission
dnu	Do not use



Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

Terminal significance	9
Ub	Voltage supply
0V	Ground
A+	Output signal channel 1
A-	Output signal channel 1 inverted
B+	Output signal channel 2 (offset by 90° to channel 1)
B-	Output signal channel 2 inverted
R+	Zero pulse (reference signal)
R-	Zero pulse inverted
nE+	System OK+ / error output
nE-	System OK- / error output inverted
SP+	DSL_OUT1 / speed switch (open collector, solid state relay on request)
SP-	DSL_OUT2 / speed switch (0V, solid state relay on request)
dnu	Do not use


Profibus-DP features	
Bus protocol	Profibus-DP V0
Features	Device Class 1 and 2
Data exchange functions	Input: Position value Output: Preset value
Preset value	The "Preset" parameter can be used to set the encoder to a predefined value that corresponds to a specific axis position of the system.
Parameter functions	Rotating direction: The relationship between the rotating direction and rising or falling output code values can be set in the operating parameter. Scaling: The parameter values set the number of steps per turn and the overall resolution.
Diagnostic	The encoder supports the following error messages: Position error
Factory setting	User address 00

Profibus-DP features	
Bus protocol	Profibus-DP V2
Features	Device Class 3 and 4
Data exchange functions	Input: Position value Output: Preset value
Preset value	The "Preset" parameter can be used to set the encoder to a predefined value that corresponds to a specific axis position of the system.
Parameter functions	Rotating direction: The relationship between the rotating direction and rising or falling output code values can be set in the operating parameter. Scaling: The parameter values set the number of steps per turn and the overall resolution.
Diagnostic	The encoder supports the following error messages: Position error
Factory setting	User address 00

Output signals

Additional output II (HTL/TTL)

At positive rotating direction (see dimension)



Trigger level

Incremental HTL/TTL

Electrically isolated:

The output TTL/HTL (Vin = Vout) at the additional output II is electrically isolated and requires a separate power supply.


Trigger level	TTL/RS422
High / Low	≥2.5 V / ≤0.5 V
Transmission length	≤550 m @ 100 kHz
Output frequency	≤600 kHz
Trigger level	TTL/HTL (Vin = Vout)
High / Low	≥2.5 V / ≤0.5 V (TTL) ≥Ub -3 V / ≤1.5 V (HTL)
Transmission length	≤550 m @ 100 kHz (TTL) ≤350 m @ 100 kHz (HTL)
Output frequency	≤600 kHz (TTL); ≤350 kHz (HTL)

Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

Switching characteristics

Speed switch



n	Speed
+ns (off)	Switch-off speed at shaft rotation in positive rotating direction (see dimension).
-ns (off)	Switch-off speed at shaft rotation in negative rotating direction (see dimension).
	Switching hysteresis ☐: 10100 % (factory setting = 10 % min. 1 Digit)
+ns (on)	Switch-on speed at shaft rotation in positive rotating direction (see dimension).
-ns (on)	Switch-on speed at shaft rotation in negative rotating direction (see dimension).

Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

98.5 14.6 14.6 179.5 69.5 86.5 67 112.5 86.5 112.5

Through hollow shaft with terminal box



Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

	HMG10	#	-	T I	4	# .	#	#	##	3	#	0 () #
Product													
Absolute encoder	HMG10												
Digital speed switch													
Without		-											
With		D											
Shaft type													
Through hollow shaft				Т									
Flange (Hollow shaft)													
Support (Support plate) for torque arm, hybrid bearings				ŀ	-								
Protection class						<u></u>							
IP 66 and IP 67, optimized for dusty, abrasive environment						D							
IP 66 and IP 67, optimized for oily, wet environment						L							
Through hollow shaft Ø16 mm, clamping ring, A end							С						
Ø20 mm, clamping ring, A end							F						
							P						
Ø16 mm, keyway Connection							۲						
Bus connecting box with 3 cable glands M16, radial								5					
Bus connecting box with 3 connectors M12, radial								3					
Bus connecting box with 3 cable glands M16, radial +								F					
terminal box with 1 cable gland M20, radial													
Bus connecting box with 3 connectors M12, radial + terminal box with 1 cable gland M20, radial								G					
Supply voltage (field bus)													
1030 VDC, Profibus-DPV0									P0				
1030 VDC, Profibus-DPV2									P2				
Resolution singleturn position										•			
13 Bit										3			
Resolution multiturn position											٥		
No multiturn signal 16 Bit											0		
											О		
Resolution speed No speed signal												0	
Resolution supplement I												U	
No additional output I												()
Resolution supplement II												•	,
No additional output II													0
512 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													1
512 ppr TTL (RS422), 6 channels													2
1024 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													5
1024 ppr TTL (RS422), 6 channels													6
2048 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													9
2048 ppr TTL (RS422), 6 channels													4
3072 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													7
3072 ppr TTL (RS422), 6 channels													8
4096 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													K
4096 ppr TTL (RS422), 6 channels													J
5000 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													
5000 ppr TTL (RS422), 6 channels													H
8192 ppr TTL/HTL push-pull (Vin=Vout), 6 channels, electrically isolated													C
8192 ppr TTL (RS422), 6 channels													P

Through hollow shaft

Profibus-DPV0 or DPV2 / 13 bit ST / 16 bit MT / Speed switch

Ordering reference

HMG10 # - T H # . # ## . 3 # 0 0 # . A

Operating temperature

-40...+85 °C

(1) Please specify the exact switching speed in addition to the part number (factory setting).

It may happen that not all variants of the type code can be combined. Any restrictions can be found in the web configurator at www.baumer.com or on request.

Accessories	
Mounting acce	ssories
11043628	Torque arm M6, length 6770 mm
11004078	Torque arm M6, length 120130 mm (≥71 mm)
11054917	Torque arm M6 insulated, length 6770 mm
11072795	Torque arm M6 insulated, length 120130 mm (≥71 mm)
11082677	Torque arm M6 insulated, length 425460 mm (≥131 mm)
11077197	Mounting kit for torque arm size M6 and earthing strap
11077087	Mounting and dismounting set

Α