

ITD 40 B10

Solid shaft $\varnothing 11$ mm with EURO flange
200...2048 pulses per revolution

Overview

- Encoder with solid shaft $\varnothing 11$ mm
- Max. 2048 pulses per revolution
- Optical sensing method
- Centering alignment $\varnothing 85$ mm, mounting screw hole circle $\varnothing 100$ mm
- Industrial standard with centering flange
- TTL or HTL output signals
- Cable output radial or axial



Technical data

Technical data - electrical ratings

Voltage supply	5 VDC ± 5 % 8...30 VDC
Reverse polarity protection	Yes
Consumption w/o load	≤ 100 mA
Pulses per revolution	200 ... 2048
Reference signal	Zero pulse, width 90°
Sensing method	Optical
Output frequency	≤ 120 kHz
Output signals	A, B, N + inverted
Output stages	TTL linedriver (short-circuit proof) HTL push-pull (short-circuit proof)
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3

Technical data - mechanical design

Size (flange)	$\varnothing 115$ mm
Shaft type	$\varnothing 11$ mm solid shaft

Technical data - mechanical design

Admitted shaft load	≤ 40 N axial ≤ 60 N radial
Flange	EURO flange B10
Protection EN 60529	IP 65
Operating speed	≤ 12000 rpm
Starting torque	≤ 0.012 Nm (+20 °C)
Material	Housing: aluminium Shaft: stainless steel
Operating temperature	-20...+70 °C -20...+100 °C
Relative humidity	90 % non-condensing
Resistance	EN 60068-2-6 Vibration 10 g, 55-2000 Hz EN 60068-2-27 Shock 100 g, 11 ms
Connection	Cable 1 m
Weight approx.	850 g

Optional

- Extended operating temperature range

ITD 40 B10

Solid shaft $\varnothing 11$ mm with EURO flange

200...2048 pulses per revolution

Terminal assignment

Core colour	Assignment
brown	Track A
green	Track A inv.
grey	Track B
pink	Track B inv.
red	Track N
black	Track N inv.
brown 0,5 mm ²	UB
white 0,5 mm ²	GND
blue	UB-Sense
white	GND-Sense
transparent	Shield/Housing

Trigger level


Outputs	Linedriver
Output level High	≥ 2.4 V
Output level Low	≤ 0.5 V
Load	≤ 70 mA

Outputs	Push-pull short-circuit proof
Output level High	$\geq U_B - 3$ V
Output level Low	≤ 1.5 V
Load	≤ 70 mA


Output signals

Clockwise rotation when looking at the mounting side.


BI-Output signals



NI-Output signals



Dimensions



025- 7

ITD 40 B10

Solid shaft ø11 mm with EURO flange

200...2048 pulses per revolution

Ordering reference

	ITD 40 B10	#####	#	####	KR1	#	11	IP65
Product	ITD 40 B10							
Pulse number								
200		200						
360		360						
500		500						
512		512						
720		720						
1000		1000						
1024		1024						
2048		2048						
Voltage supply / signals								
5 VDC / TTL level, linedriver			T					
8...30 VDC / HTL level, push-pull			H					
8...30 VDC / TTL level, linedriver			R					
Output signals								
A, A inv, B, B inv				BI				
A, A inv, B, B inv, N, N inv				NI				
Connection								
Cable 1 m, radial					KR1			
Operating temperature								
-20...+70 °C						S		
-20...+100 °C						E		
Flange / Solid shaft								
EURO flange B10 / ø11 mm							11	
Protection								
IP 65								IP65