


EIL580P-SY - M23 CW

Solid shaft with synchro flange, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Overview

- Size ø58 mm
- Precise optical sensing (interpolated)
- Output signal level programmable (TTL or HTL)
- Synchro flange
- Connection flange connector M23 CW axial or radial
- Pulses per revolution 1...65536, programmable
- High protection up to IP 67
- High resistance to shock and vibrations



Technical data

Technical data - electrical ratings

Voltage supply	4.75...30 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes
Consumption w/o load	≤70 mA
Initializing time	≤ 30 ms after power on
Pulses per revolution	1 ... 65536
Duty cycle	45...55 % typical at 1024, 2048 ppr (further see table Duty cycle)
Reference signal	Zero pulse 90° or 180°
Sensing method	Optical
Output frequency	≤300 kHz (TTL) ≤160 kHz (HTL)
Output signals	A+, B+, R+, A-, B-, R-
Output stages	TTL/RS422 HTL/push-pull
Programmable parameters	Output level TTL/HTL Pulse number 1...65536 Zero pulse width 90°/180° Zero pulse position Signal sequence
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Approval	UL 508 / CSA 22.2

Technical data - mechanical design

Size (flange)	ø58 mm
Shaft type	ø6 x 10 mm, solid shaft with flat
Admitted shaft load	≤40 N axial ≤80 N radial
Flange	Synchro flange
Protection EN 60529	IP 65 (without shaft seal) IP 67 (with shaft seal)
Operating speed	≤6000 rpm (+20 °C, IP 67) ≤12000 rpm (+20 °C, IP 65)
Starting torque	≤0.015 Nm (+20 °C, IP 65) ≤0.02 Nm (+20 °C, IP 67)
Material	Housing: aluminium die-cast Flange: aluminium Solid shaft: stainless steel
Operating temperature	-40...+100 °C
Relative humidity	90 % non-condensing
Resistance	EN 60068-2-6 Vibration 30 g, 10-2000 Hz EN 60068-2-27 Shock 300 g, 6 ms
Connection	Flange connector M23, 12-pin
Weight approx.	300 g

EIL580P-SY - M23 CW

Solid shaft with synchro flange, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)


Terminal assignment

Flange connector M23, 12-pin, clockwise (CW)

Pin	Assignment
1	B-
2	—
3	R+
4	R-
5	A+
6	A-
7	R-Set ¹⁾
8	B+
9	—
10	GND
11	—
12	UB

¹⁾ The R-Set input is used to set the reference pulse (zero pulse) on the current shaft position.


R-Set = UB ≥ 200 ms




Flange connector M23, pin contacts, 12-pin, clockwise (CW)

Output signals

Zero pulse electrical 90° A&B high
(Factory setting at clockwise rotation (CW)
in view of the encoder flange)



Zero pulse electrical 180° B low
(at clockwise rotation (CW)
in view of the encoder flange)



Trigger level

Outputs	TTL/RS422
Output level High	≥2.5 V
Output level Low	≤0.5 V
Load	≤20 mA

Outputs	HTL/Push-pull
Output level High	≥UB -3 V
Output level Low	≤1.5 V
Load	≤20 mA

EIL580P-SY - M23 CW

Solid shaft with synchro flange, flange connector M23 CW


1...65536 pulses per revolution programmable (interpolated system)

Duty cycle

The duty cycle (D) is defined as the time ratio between the HIGH pulse duration (H) and the pulse period (T).

System-induced and depending on the pulse number, the measured values may vary which has an impact on speed and position acquisition.

Binary pulse numbers are recommended for speed feedback.




Programmed pulse number	Scan ratio (D) (maximum)	Jitter (+/-) (maximum)
1...1023	45...55 %	5%
1024, 2048	45...55 %	5%
1025...5000	40...60 %	10%
8192, 16384	35...85 %	15%
5001...10000	22...78 %	28%
32768	25...75 %	25%
65536	15...85 %	35%
all other	Jitter[%]=(programmed pulse number -10000)*0,0007%+28%	

EIL580P-SY - M23 CW


Solid shaft with synchro flange, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Dimensions



Synchro flange, flange connector M23, radial



Synchro flange, flange connector M23, axial

EIL580P-SY - M23 CW

Solid shaft with synchro flange, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Ordering reference

		EIL580P	-	S	Y	##	.	#	##	#	.	01024	.	B
Product		EIL580P												
Shaft type														
Solid shaft				S										
Flange (shaft)														
Synchro flange, centering collar ø50 x 4 mm, flute ø53 mm, pitch circle diameter ø42 - 3xM3/3xM4					Y									
Shaft														
ø6 x 10 mm, with flat								06						
ø3/8 x 4/5 (Ø9.525 x 20.32 mm), with flat								U3						
Protection class														
IP 65									5					
IP 67									7					
Connection														
Flange socket radial, M23, 12-pin, male contacts, CW										E				
Flange socket axial, M23, 12-pin, male contacts, CW										C				
Voltage supply / output														
4,75...30 VDC, TTL/RS422 6 channel (Vout=5V)											F			
4,75...30 VDC, HTL/push pull, 6 channel (Vout=Vin)											Q			
Pulses programmable														
1...65536 programmable (factory setting: 1024)												01024		
Operating temperature														B
-40...+100 °C														

(Factory setting: 1024 ppr, Vout = 5 VDC TTL, signal sequence A leading B (CW), zero pulse 90° A&B high)

Accessories

Mounting accessories

11065916	Coupling CPS25 (L=19, D1=06 / D2=06)
11065917	Coupling CPS25 (L=19, D1=06 / D2=08)
11065922	Coupling CPS25 (L=19, D1=10 / D2=06)
11065926	Coupling CPS25 (L=19, D1=11 / D2=06)
11065928	Coupling CPS25 (L=19, D1=12 / D2=06)
10141131	Spring washer coupling (D1=6 / D2=6)
10141132	Spring washer coupling (D1=6 / D2=10)
11034139	Spring washer coupling (D1=6 / D2=16)
11050507	Bellows coupling (D1=06 / D2=10)
10117667	Mounting adaptor
10117668	Set of eccentric fixings for mounting clamp (10117667)
11065545	Set of eccentric fixings type A
10158124	Bearing flange for encoders with synchro flange (Z 119.035)

Programming accessories

11120657	Handheld Programming Tool Z-PA-EI-H
11120547	PC Programming Tool Z-PA-EI-P
11222569	Connection cable connector M23 (CCW) / connector D-SUB, 0.2 m
11222570	Connection cable connector M23 (CCW) / connector D-SUB, 1 m