

EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW
100...5000 pulses per revolution

Overview

- Size ø58 mm
- Precise optical sensing
- Output signal level TTL or HTL
- Blind hollow shaft, ø8...15 mm
- Connection flange connector M23 CW axial or radial
- Pulses per revolution up to 5000
- High protection up to IP 67
- High resistance to shock and vibrations



Technical data

Technical data - electrical ratings

Voltage supply	5 VDC ±5 % 8...30 VDC 4.75...30 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes (HTL) Yes (TTL, max. 1 s and 1 signal)
Consumption w/o load	≤70 mA
Pulses per revolution	100 ... 5000
Phase shift	90 ° ±10°
Duty cycle	40...60 %
Reference signal	Zero pulse, width 90° ±10 %
Sensing method	Optical
Output frequency	≤300 kHz (TTL) ≤160 kHz (HTL)
Output signals	A+, B+, R+, A-, B-, R-
Output stages	TTL/RS422 HTL/push-pull
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Approval	UL 508 / CSA 22.2

Technical data - mechanical design

Size (flange)	ø58 mm
Shaft type	ø8...15 mm (blind hollow shaft) ø9.52 mm (blind hollow shaft) ø12.7 mm (blind hollow shaft)
Protection EN 60529	IP 65 (without shaft seal) IP 67 (with shaft seal)
Operating speed	≤6000 rpm (+20 °C, IP 67) ≤8000 rpm (+20 °C, IP 65)
Starting torque	≤0.02 Nm (+20 °C, IP 65) ≤0.025 Nm (+20 °C, IP 67)
Material	Housing: aluminium die-cast Flange: aluminium
Operating temperature	-40...+85 °C
Relative humidity	90 % non-condensing
Resistance	EN 60068-2-6 Vibration 30 g, 10-2000 Hz EN 60068-2-27 Shock 250 g, 6 ms
Connection	Flange connector M23, 12-pin
Weight approx.	300 g


EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW
100...5000 pulses per revolution

Terminal assignment

Flange connector M23, 12-pin, clockwise (CW)

Pin	Assignment
1	B-
2	—
3	R+
4	R-
5	A+
6	A-
7	—
8	B+
9	—
10	GND
11	—
12	UB



Flange connector M23,
pin contacts, 12-pin,
clockwise (CW)


Trigger level

Outputs	TTL/RS422
Output level High	$\geq 2.5 \text{ V}$
Output level Low	$\leq 0.5 \text{ V}$
Load	$\leq 20 \text{ mA}$

Outputs	HTL/Push-pull
Output level High	$\geq U_B - 3 \text{ V}$
Output level Low	$\leq 1.5 \text{ V}$
Load	$\leq 20 \text{ mA}$

Output signals


Clockwise rotating direction when looking at flange.




EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW
100...5000 pulses per revolution


Dimensions



Clamping ring at A-side: Blind hollow shaft, flange connector M23 radial



Clamping ring at A-side: Blind hollow shaft, flange connector M23 axial




Flange version M: Mounting position torque support


EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW
100...5000 pulses per revolution

Dimensions



Flange version P: Pin torque support, axial, clamping ring at A-side



Blind hollow shaft

EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW
 100...5000 pulses per revolution

Ordering reference

	EIL580	-	B	#	##	.	#	##	#	.	#####	.	A
Product	EIL580												
Shaft type													
Blind hollow shaft				B									
Flange (Hollow shaft)													
Without stator coupling					N								
With stator coupling, 1-armed, hole circle ø63...94 mm, M4, mounting position 180°					M								
With stator coupling ø63 mm					T								
Pin torque support 3 mm, axial/radial					P								
Blind hollow shaft													
ø8 mm, clamping ring, A-side					08								
ø3/8" (ø9.52 mm), clamping ring, A-side					U3								
ø10 mm, clamping ring, A-side					10								
ø12 mm, clamping ring, A-side					12								
ø1/2" (ø12.7 mm), clamping ring, A-side					U4								
ø14 mm, clamping ring, A-side					14								
ø15 mm, clamping ring, A-side					15								
Protection class													
IP 65								5					
IP 67								7					
Connection													
Flange socket radial, M23, 12-pin, male contacts, CW								E					
Flange socket axial, M23, 12-pin, male contacts, CW								C					
Voltage supply / output													
5 VDC, TTL/RS422, 6 channel								E					
8...30 VDC, TTL/RS422, 6 channel (Vout=5V)								H					
8...30 VDC, HTL/push pull, 6 channel								N					
4,75...30 VDC, HTL/push pull, 6 channel (Vout=Vin)								Q					

EIL580-B - M23 CW

With blind hollow shaft, flange connector M23 CW

100...5000 pulses per revolution

Ordering reference

	EIL580	-	B	#	##	.	#	##	#	.	#####	.	A
Pulses per revolution													
100													100
120													120
150													150
200													200
250													250
256													256
300													300
360													360
400													400
440													440
500													500
512													512
600													600
720													720
800													800
900													900
1000													1000
1024													1024
1200													1200
1250													1250
1440													1440
1500													1500
1800													1800
2000													2000
2048													2048
2500													2500
3000													3000
3600													3600
4000													4000
4096													4096
5000													5000
Operating temperature													
-40...+85 °C													A

Accessories

Mounting accessories

11066083	Torque arm, 1-arm (mounting kit 006)
11073119	Torque arm, 1-arm (mounting kit 021)
11067367	Torque arm, 1-arm (mounting kit 028)
11100198	Stator coupling, 2-armed (mounting kit 046)
11113210	Torque arm, 1-arm (mounting kit 047)
11124300	Torque arm, 1-arm (mounting kit 048)
11155325	Rigid mounting plate, 1-arm (mounting kit 099)
11106627	Fan cover clip 8 mm
11094674	Clamping ring 12/31/ 8 M3 8.8
11094675	Clamping ring 17/31/ 8 M3 8.8
11116921	Insulating sleeve ø10 mm/ø12 mm/25 mm long
11116923	Insulating sleeve ø12 mm/ø14 mm/25 mm long