

EIL580P-B - M23 CW

With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Overview

- Size ø58 mm
- Precise optical sensing (interpolated)
- Output signal level programmable (TTL or HTL)
- Blind hollow shaft, ø8...15 mm
- Connection flange connector M23 CW axial or radial
- Pulses per revolution 1...65536, programmable
- High protection up to IP 67
- High resistance to shock and vibrations



Technical data

Technical data - electrical ratings

Voltage supply	4.75...30 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes
Consumption w/o load	≤70 mA
Initializing time	≤ 30 ms after power on
Pulses per revolution	1 ... 65536
Duty cycle	45...55 % typical at 1024, 2048 ppr (further see table Duty cycle)
Reference signal	Zero pulse 90° or 180°
Sensing method	Optical
Output frequency	≤300 kHz (TTL) ≤160 kHz (HTL)
Output signals	A+, B+, R+, A-, B-, R-
Output stages	TTL/RS422 HTL/push-pull
Programmable parameters	Output level TTL/HTL Pulse number 1...65536 Zero pulse width 90°/180° Zero pulse position Signal sequence
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3

Technical data - electrical ratings

Approval	UL 508 / CSA 22.2
----------	-------------------

Technical data - mechanical design

Size (flange)	ø58 mm
Shaft type	ø8...15 mm (blind hollow shaft) ø9.52 mm (blind hollow shaft) ø12.7 mm (blind hollow shaft)
Protection EN 60529	IP 65 (without shaft seal) IP 67 (with shaft seal)
Operating speed	≤6000 rpm (+20 °C, IP 67) ≤8000 rpm (+20 °C, IP 65)
Starting torque	≤0.02 Nm (+20 °C, IP 65) ≤0.025 Nm (+20 °C, IP 67)
Material	Housing: aluminium die-cast Flange: aluminium
Operating temperature	-40...+100 °C
Relative humidity	90 % non-condensing
Resistance	EN 60068-2-6 Vibration 30 g, 10-2000 Hz EN 60068-2-27 Shock 250 g, 6 ms
Connection	Flange connector M23, 12-pin
Weight approx.	300 g

EIL580P-B - M23 CW

With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)


Terminal assignment

Flange connector M23, 12-pin, clockwise (CW)

Pin	Assignment
1	B-
2	—
3	R+
4	R-
5	A+
6	A-
7	R-Set ¹⁾
8	B+
9	—
10	GND
11	—
12	UB

¹⁾ The R-Set input is used to set the reference pulse (zero pulse) on the current shaft position.


R-Set = UB ≥ 200 ms




Flange connector M23, pin contacts, 12-pin, clockwise (CW)

Output signals

Zero pulse electrical 90° A&B high
(Factory setting at clockwise rotation (CW)
in view of the encoder flange)



Zero pulse electrical 180° B low
(at clockwise rotation (CW)
in view of the encoder flange)



Trigger level

Outputs	TTL/RS422
Output level High	≥2.5 V
Output level Low	≤0.5 V
Load	≤20 mA
Outputs	HTL/Push-pull
Output level High	≥UB -3 V
Output level Low	≤1.5 V
Load	≤20 mA

EIL580P-B - M23 CW

With blind hollow shaft, flange connector M23 CW


1...65536 pulses per revolution programmable (interpolated system)

Duty cycle

The duty cycle (D) is defined as the time ratio between the HIGH pulse duration (H) and the pulse period (T).

System-induced and depending on the pulse number, the measured values may vary which has an impact on speed and position acquisition.

Binary pulse numbers are recommended for speed feedback.




Programmed pulse number	Scan ratio (D) (maximum)	Jitter (+/-) (maximum)
1...1023	45...55 %	5%
1024, 2048	45...55 %	5%
1025...5000	40...60 %	10%
8192, 16384	35...85 %	15%
5001...10000	22...78 %	28%
32768	25...75 %	25%
65536	15...85 %	35%
all other	Jitter[%]=(programmed pulse number -10000)*0,0007%+28%	

EIL580P-B - M23 CW


With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)


Dimensions



Clamping ring at A-side: Blind hollow shaft, flange connector M23 radial



Clamping ring at A-side: Blind hollow shaft, flange connector M23 axial




Flange version M: Mounting position torque support

EIL580P-B - M23 CW


With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Dimensions



Flange version P: Pin torque support, axial, clamping ring at A-side



Blind hollow shaft

EIL580P-B - M23 CW

With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Ordering reference

	EIL580P	-	B	#	##	.	#	##	#	.	01024	.	B
Product	EIL580P												
Shaft type													
Blind hollow shaft			B										
Flange (Hollow shaft)													
Without stator coupling				N									
With stator coupling, 1-armed, hole circle ø63...94 mm, M4, mounting position 180°				M									
With stator coupling ø63 mm				T									
Pin torque support 3 mm, axial/radial				P									
Blind hollow shaft													
ø8 mm, clamping ring, A-side					08								
ø3/8" (ø9.52 mm), clamping ring, A-side					U3								
ø10 mm, clamping ring, A-side					10								
ø12 mm, clamping ring, A-side					12								
ø1/2" (ø12.7 mm), clamping ring, A-side					U4								
ø14 mm, clamping ring, A-side					14								
ø15 mm, clamping ring, A-side					15								
Protection class													
IP 65							5						
IP 67							7						
Connection													
Flange socket radial, M23, 12-pin, male contacts, CW								E					
Flange socket axial, M23, 12-pin, male contacts, CW								C					
Voltage supply / output													
4,75...30 VDC, TTL/RS422 6 channel (Vout=5V)								F					
4,75...30 VDC, HTL/push pull, 6 channel (Vout=Vin)								Q					
Pulses programmable													
1...65536 programmable (factory setting: 1024)											01024		
Operating temperature													
-40...+100 °C													B

(Factory setting: 1024 ppr, Vout = 5 VDC TTL, signal sequence A leading B (CW), zero pulse 90° A&B high)

Accessories

Mounting accessories

11066083	Torque arm, 1-arm (mounting kit 006)
11073119	Torque arm, 1-arm (mounting kit 021)
11067367	Torque arm, 1-arm (mounting kit 028)
11100198	Stator coupling, 2-armed (mounting kit 046)
11113210	Torque arm, 1-arm (mounting kit 047)
11124300	Torque arm, 1-arm (mounting kit 048)
11155325	Rigid mounting plate, 1-arm (mounting kit 099)
11106627	Fan cover clip 8 mm
11094674	Clamping ring 12/31/ 8 M3 8.8
11094675	Clamping ring 17/31/ 8 M3 8.8
11116921	Insulating sleeve ø10 mm/ø12 mm/25 mm long
11116923	Insulating sleeve ø12 mm/ø14 mm/25 mm long

EIL580P-B - M23 CW

With blind hollow shaft, flange connector M23 CW

1...65536 pulses per revolution programmable (interpolated system)

Accessories

Programming accessories

11120657	Handheld Programming Tool Z-PA-EI-H
11120547	PC Programming Tool Z-PA-EI-P
11222569	Connection cable connector M23 (CCW) / connector D-SUB, 0.2 m
11222570	Connection cable connector M23 (CCW) / connector D-SUB, 1 m