


## Overview

- M12, female, A-coded, 5-poles; PUR, 1500 cm, free cable end
- Dragchain capable; suitable for robotics  $\pm 180^\circ/\text{m}$
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames, oils
- Halogen free



## Technical data

### Side A

|                              |                                       |
|------------------------------|---------------------------------------|
| Head A: Connection           | M12                                   |
| Head A: Angle cable outlet   | 0°                                    |
| Head A: Gender               | Female                                |
| Head A: Coding               | A                                     |
| Head A: No. of poles         | 5                                     |
| Head A: LED                  | No                                    |
| Head A: Width across flats   | AF13                                  |
| Head A: Tightening torque    | 0.6 Nm                                |
| Head A: Knurled nut material | Zinc-pressure die casting, surface Ni |
| Head A: Body color           | Black                                 |
| Head A: Gasket material      | FKM                                   |
| Labeling sleeve side A       | Yes                                   |

### Side B

|                        |                  |
|------------------------|------------------|
| Head B: Connection     | Open-ended wires |
| Labeling sleeve side B | Yes              |

### Cables

|                           |                      |
|---------------------------|----------------------|
| Cable length              | 1500 cm              |
| Length tolerance          | $\pm 22.5$ cm        |
| Stripping length          | 20 mm                |
| Shielded                  | No                   |
| Conductor structure       | 42 $\times$ 0.1 mm   |
| AWG                       | 22                   |
| External sheath: Material | PUR                  |
| External sheath: Color    | Black                |
| Cable diameter            | 4.8 mm $\pm$ 5%      |
| Wire cross section        | 0.34 mm <sup>2</sup> |

### Electrical data

|                                    |                  |
|------------------------------------|------------------|
| Operating voltage                  | max. 125 V AC/DC |
| Operating voltage (only UL listed) | 30 V AC/DC       |
| Nominal voltage                    | 300 V            |
| Contact resistance                 | max. 30 mOhm     |
| Operating current per contact      | max. 4 A         |

### Mechanical data

|                                 |                                 |
|---------------------------------|---------------------------------|
| Head A: Degree of protection    | IP65, IP66K, IP67               |
| Bending radius (mobile)         | min. 10 $\times$ outer diameter |
| Bending radius (fixed)          | min. 5 $\times$ outer diameter  |
| No. of bending cycles (C-track) | approx. 10000000 Cycles         |
| Torsion speed                   | max. 35 cycles/min              |
| Torsion stress in °             | $\pm 180^\circ/\text{m}$        |
| No. of torsion cycles           | approx. 2000000 Cycles          |
| Acceleration (C-track)          | max. 10 m/s <sup>2</sup>        |
| Travel speed (C-track)          | max. 3 m/s                      |

### Environmental conditions


|                                   |                                                     |
|-----------------------------------|-----------------------------------------------------|
| Temperature range (mobile)        | - 25 ...+ 80 °C                                     |
| Temperature range (fixed)         | - 25 ...+ 80 °C                                     |
| Cable: Temperature range (fixed)  | - 40 ...+ 80 °C                                     |
| Dragchain capable                 | Yes                                                 |
| Head A: Chemical resistance       | No                                                  |
| Head A: Flame resistance          | HB (UL 94)                                          |
| Head A: Oil resistance            | ASTM 1 oil, mineral oils, limited to hydraulic oils |
| Head A: Acid and alkali resistant | No                                                  |
| Head A: Pollution degree          | 3                                                   |
| Cable: Chemical resistance        | Good (DIN EN 60811-404)                             |
| Cable: Flame resistance           | Conform UL 1581 §1090 (H), CSA FT2, IEC 60332-2-2   |
| Cable: Oil resistance             | Good (DIN EN 60811-404)                             |
| Cable: Silicone-free              | Yes                                                 |

### Commercial data


|        |          |
|--------|----------|
| Eclass | 27060311 |
|--------|----------|

## Side A


### Technical drawing




## Connection diagram



## Coding



## Dimension drawing



## Side B

### Technical drawing

