

LXC-120C

Camera Link, 12 Megapixel, Color

Article number: 11148664

Overview

- 4096 × 3072 px
- ams (CMOSIS) CMV12000
- APS-C CMOS
- 63 fps
- Camera Link Full



Picture similar



GEN*i*CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV12000
Mono/Color	Color
Color filter	RGB Bayer Mosaic
Sensor type	APS-C CMOS
Shutter type	Global shutter
Resolution	4096 × 3072 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.02 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	12.89 e-
Saturation capacity	8845 e-
Dynamic range	56.2 dB
Signal-to-noise ratio	39.5 dB
Quantum efficiency	33.8 % @ 465 nm 33.2 % @ 536 nm 33 % @ 631 nm

Acquisition formats

Image formats, interface	Full Frame, 4096 × 3072 px, max. 63 fps frame rate max.
Pixel formats	BayerGB8 BayerGB10

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Raw Bayer
Color processing	NA

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	1 output line
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Camera Link Full, connector: 2 x Standard SDR26 (Mini CL)
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm

LXC-120C

Camera Link, 12 Megapixel, Color

Article number: 11148664

Technical data

Mechanical data

Depth	43.05 mm
Weight	≤ 235 g (M58-mount)
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 38 ... 57 V (PoCL)
Power consumption	Approx. 6.5 W @ 24 VDC Approx. 6.5 W @ 12 VDC (PoCL)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)

Protection class	IP 40
------------------	-------

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

