

Absolute encoders - bus interfaces

Ex approval Ex II 2D/2G (ATEX)

Optical multiturn encoders 13 bit ST / 16 bit MT

X 700 - Profibus



X 700 with Profibus

Features

- Encoder multiturn / Profibus / ATEX
- Optical sensing method
- Resolution: singleturn 13 bit, multiturn 16 bit
- Clamping flange with solid shaft $\varnothing 10$ mm
- Explosion protection per Ex II 2D/2G (ATEX)
- Device class 2 / zone 1 (gas), zone 21 (dust)
- Maximum resistant against magnetic fields

Technical data - electrical ratings

Voltage supply	10...30 VDC
Reverse polarity protection	Yes
Consumption w/o load	≤ 100 mA (24 VDC)
Initializing time typ.	250 ms after power on
Interface	Profibus-DPV0
Function	Multiturn
Device adress	Rotary switches in bus cover
Steps per revolution	≤ 8192 / 13 bit
Number of revolutions	≤ 65536 / 16 bit
Absolute accuracy	$\pm 0.025^\circ$
Sensing method	Optical
Code	Binary
Code sequence	CW/CCW programmable
Interference immunity	DIN EN 61000-6-2
Emitted interference	DIN EN 61000-6-4
Programmable parameters	Operating modes Total resolution Scaling Rotation speed monitoring
Diagnostic functions	Position or parameter error Multiturn sensing

Technical data - mechanical design

Size (flange)	$\varnothing 70$ mm
Shaft type	$\varnothing 10$ mm solid shaft (clamping flange)
Flange	Clamping flange
Protection DIN EN 60529	IP 67
Operating speed	≤ 6000 rpm (mechanical) ≤ 6000 rpm (electric)
Starting acceleration	≤ 1000 U/s ²
Starting torque	≤ 0.4 Nm (+25 °C)
Admitted shaft load	≤ 60 N axial ≤ 50 N radial
Materials	Housing: stainless steel Flange: stainless steel
Operating temperature	-20...+70 °C
Relative humidity	95 % non-condensing
Resistance	DIN EN 60068-2-6 Vibration 10 g, 16-2000 Hz DIN EN 60068-2-27 Shock 200 g, 6 ms
Explosion protection	Ex II 2G Ex d IIC T6 Ex II 2D
Weight approx.	1500 g
Connection	Bus cover

Absolute encoders - bus interfaces

Ex approval Ex II 2D/2G (ATEX)

Optical multiturn encoders 13 bit ST / 16 bit MT

X 700 - Profibus

Part number

X 700.P	1	1	3P33
			Interface
			3P33 Profibus-DPV0 / cable gland
			Voltage supply / signals
	1		10...30 VDC / 13 + 16 bit
			Flange / Solid shaft
	1		Clamping flange / ø10 mm, IP 67

CD with file descriptions is not included in the delivery. You may order them on CD as accessory.

Accessories

Programming accessories

10146710	CD with describing files & manuals (Z 150.022)
----------	--

Profibus-DP features

Bus protocol	Profibus-DPV0
Device profile	Device Class 1 and 2
Cyclic data exchange	Communication in line with DPV0
Input data	Position value. In addition optionally speed signal parametering (output of current rotation speed).
Output data	Preset
Preset	Parameter for setting the encoder to a requested position value assigned to a defined shaft position of the system. Storage non-volatile.
Rotating direction	Parameter for defining the rotating direction in which there have to be ascending or descending position values.
Scaling	Parameter defining the steps per turn as well as the total resolution.
Diagnosis	The encoder supports the following error warnings: - Position and parameter error - Lithium battery voltage control (Multiturn)
Default	User address 00 Termination OFF


Absolute encoders - bus interfaces

Ex approval Ex II 2D/2G (ATEX)

Optical multiturn encoders 13 bit ST / 16 bit MT

X 700 - Profibus

View inside bus cover




Terminal assignment


Cable gland	
UB	Voltage supply 10...30 VDC
GND	Ground connection relating to UB
A	Negative data line
B	Positive data line

Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections UB-UB and GND-GND is 1 A each.


Termination



User address (identifier)



Dimensions



The electrical outlet may provide a $\pm 15^\circ$ shift to the bore pattern

Absolute encoders - bus interfaces

Ex approval Ex II 2D/2G (ATEX)

Optical multiturn encoders 13 bit ST / 16 bit MT

X 700 - Profibus

Checklist for EX protection data collection

For the design of explosion-proof encoders of the IX700 or AX700 series according to EU Directive 2014/34/EU, it is absolutely necessary to complete this checklist in order to be able to resolve all open questions regarding explosion protection and application conscientiously.

Company: _____

Address: _____

Department: _____ Phone: _____

Clerck/Technician: _____

Email: _____

Responsibility:

The operator is responsible for maintaining the performance limit of the devices (see datasheet)

Equipment group:			Please select
Classification according to ATEX 2021/34/EU	Equipment group I	Mining M2	
	Equipment group II	Explosive Atmosphere	
Classification according to IEC 60079	Equipment group I	Mining M2	
	Equipment group II	Gas hazardous areas	
	Equipment group III	Dust hazardous areas	

Equipment Use / Field Application: (i.e.: paint line, process engineering, gas storage etc.)

X 700 - Incremental			
Ambient temperature range	Temperature class	max. surface temperature on the housing	Enter value
-20°C bis +55°C	T6	+85°C	
-20°C bis +105°C	T4	+135°C	
dust: -20°C bis +45°C	T70		

X 700 - Absolute			
Ambient temperature range	Temperature class	max. surface temperature on the housing	Enter value
-20°C bis +65°C	T6	+85°C	
-20°C bis +115°C	T4	+135°C	
Dust: -20°C bis +55°C	T70		

Mechanical load			Enter values
Numbers of revolutions:	RMP	max. 3000 rpm	
Axial shaft load:	(N)		
Radial shaft load:	(N)		
Environmental influences (salt, alkalis, etc.):			

Date:	Stamp:
Signature:	

Internal information (to be filled in by Baumer)

Baumer order number:

Baumer production order number