27/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Spindle position displays

Through hollow shaft uo to ø14 mm, manual format adjustment Display LCD two lines, interface RS485

N 150



N 150 with connector output

Features

- Manual format adjustment
- Through hollow shaft up to ø14 mm
- Resolution: 1440 steps/revolution ±4096 revolutions
- Display: LCD backlit, two lines
- Absolute multiturn measuring system
- Actual value and target display
- Interface RS485

Technical data - electrical ratings		
Voltage supply	24 VDC ±10 %	
Current consumption	≤30 mA	
Display	LCD, 7-segment display, 2-lines, backlit	
Measuring principle	Absolute multiturn measuring system	
Measuring range	-99.99+999.99 mm -9.999+99.999 inch	
Steps per revolution	1440	
Number of revolutions	4096 / 12 bit	
Spindle pitch	≤14 mm	
Interface	RS485 (ASCII protocol)	
Data memory	Parameter buffer: EEPROM Current value buffer: >10 years by integrated 3 V lithium battery	
Programmable parameters	Display position horizontal/ vertical Measuring unit mm/inch Counting direction Spindle pitch Spindle tolerance Positioning direction Direction arrows Tolerance window Round up/down	
Standard DIN EN 61010-1	Protection class II Overvoltage category II Pollution degree 2	
Emitted interference	DIN EN 61000-6-3	
Interference immunity	DIN EN 61000-6-2	
Approval	UL approval / E63076	


Technical data - mechanical design		
Shaft type	ø14 mm (through hollow shaft)	
Operating speed	≤600 rpm (short-term)	
Protection DIN EN 60529	IP 50	
Operating temperature	-10+50 °C	
Storage temperature	-20+70 °C	
Relative humidity	80 % non-condensing	
Torque support	Torque pin provided at housing	
Connection	 - Male/female connector M8, 4-pin - Cable output (30/15 cm) with male/female connector M8, 4-pin 	
Housing type	Surface-mount with hollow shaft	
Dimensions	37 x 75 x 45 mm	
Mounting type	Directly at shaft end by means of grub screw	
Weight approx.	120 g	
Material	Polyamide black, UL 94V-0	

27/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Spindle position displays

Through hollow shaft uo to ø14 mm, manual format adjustment Display LCD two lines, interface RS485

N 150



Description		
Ν	150 spindle	
in	manual en	

le position display supports the editing engineer in manual spindle positioning. The principal benefits of the new electronic spindle position display are saving time in machine setup and editing as well as eliminating errors when aligning formats to new position values. The absolute measuring system captures any change in position even in powerless state. The backlit LCD display provides the editing engineer with all necessary information for efficient editing of new spindle positions. The two-line display shows both current value and target. A little arrow signalizes the editing engineer the direction the spindle must be turned to get to the new position.

RS485 serial interface enables network of maximum 32 spindle position displays to PC or PLC.

Accessories		
Connectors and cables		
11034330	Adaptor cable between cable connector M8 and female M16, 1 m (Z 178.A01)	
10159563	Cable connector M8, 4-pin, without cable with integrated terminating resistor 120 Ω (Z 178. AW1)	
10160606	Female connector M8, 4-pin, without cable (Z 178.B01)	
10159560	Data and supply cable M8, 5 m (Z 178.D05)	
10160605	Cable connector M8, 4-pin, without cable (Z 178.S01)	
10159739	Coupling cable with M8 - M8, 1 m cable (Z 178.V01)	
11034336	Coupling cable with M8 - M8, 3 m cable (Z 178.V03)	
11034337	Coupling cable with M8 - M8, 5 m cable (Z 178.V05)	
11034338	Coupling cable with M8 - M8, 10 m cable (Z 178.V10)	
10160607	Data and supply cable, ø5 mm, 4 cores, shielded, on 50 m drum (Z 178.050)	

27/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Spindle position displays

Through hollow shaft uo to ø14 mm, manual format adjustment Display LCD two lines, interface RS485

N 150

Terminal assignment Connector Assignment Pin 1 Tx/Rx-, RS485 Pin 2 Tx/Rx+, RS485 Pin 3 Sensor supply +24 V Pin 4 Sensor supply 0 V M8 connector M8 female connector

Dimensions

