318 Subject to modification in technic and design. Errors and omissions except

Spindle position displays

Through hollow shaft up to ø14 mm, automated format adjustment Display LCD two lines, interface RS485

N 152



N 152 with cable output

Features

- Automated format adjustment
- Two keys for format adjustment touch by touch
- Through hollow shaft up to ø14 mm
- Resolution: 1440 steps/revolution ±4096 revolutions
- Display: LCD backlit, two lines
- Absolute multiturn measuring system
- Actual value and target display
- Interface RS485


Technical data - electrical ratings	
Voltage supply	24 VDC ±10 %
Current consumption	≤40 mA
Display	LCD, 7-segment display, 2-lines, backlit
Measuring principle	Absolute multiturn measuring system
Measuring range	-99.99+999.99 mm -9.999+99.999 inch
Steps per revolution	1440
Number of revolutions	4096 / 12 bit
Spindle pitch	≤14 mm
Interface	RS485 (ASCII protocol)
Data memory	Parameter buffer: EEPROM Current value buffer: >10 years by integrated 3 V lithium battery
Programmable parameters	Display position horizontal/ vertical Measuring unit mm/inch Counting direction Spindle pitch Spindle tolerance Positioning direction Direction arrows Tolerance window Round up/down
Motive positioning	Two softkeys for format alignment Direct motor connection to N 152 by motor cable
Standard DIN EN 61010-1	Protection class II Overvoltage category II Pollution degree 2
Emitted interference	DIN EN 61000-6-3
Interference immunity	DIN EN 61000-6-2

Technical data - mechanical design	
Shaft type	ø14 mm (through hollow shaft)
Operating speed	≤600 rpm (short-term)
Protection DIN EN 60529	IP 50
Operating temperature	-10+50 °C
Storage temperature	-20+70 °C
Relative humidity	80 % non-condensing
Torque support	Torque pin provided at housing
Connection	- Cable output (15 cm) with male connector M8, 4-pin - Motor cable with female connector M16, 12-pin
Operation / keypad	Membrane with two keys
Housing type	Surface-mount with hollow shaft
Dimensions	37 x 75 x 45 mm
Mounting type	Directly at shaft end by means of grub screw
Weight approx.	120 g
Material	Polyamide black, UL 94V-0

Spindle position displays

Through hollow shaft up to ø14 mm, automated format adjustment Display LCD two lines, interface RS485

N 152



Accessories		
Connectors and cables		
11034330	Adaptor cable between cable connector M8 and female M16, 1 m (Z 178.A01)	
10159563	Cable connector M8, 4-pin, without cable with integrated terminating resistor 120 Ω (Z 178. AW1)	
10160606	Female connector M8, 4-pin, without cable (Z 178.B01)	
10159560	Data and supply cable M8, 5 m (Z 178.D05)	
11054456	Extension cable SPA-motor (male/female) M16, 12-pin, 1 m (Z 165.E01)	
10160605	Cable connector M8, 4-pin, without cable (Z 178.S01)	
10159739	Coupling cable with M8 - M8, 1 m cable (Z 178.V01)	
11034339	Y-junction M8, 4-pin, with cable (Z 178.Y02)	
11034336	Coupling cable with M8 - M8, 3 m cable (Z 178.V03)	
11034337	Coupling cable with M8 - M8, 5 m cable (Z 178.V05)	
11034338	Coupling cable with M8 - M8, 10 m cable (Z 178.V10)	
10160607	Data and supply cable, ø5 mm, 4 cores, shielded, on 50 m drum (Z 178.050)	

Description

multiconDrive represents a simplified and very efficient, reasonably priced system for automatic format adjustment. With multiconDrive the spindle position displays communicate directly with EC motors. Every spindle position display is connected to the corresponding motor by a separate cable output providing the motor without delay with the signals "clockwise", "counterclockwise", "rotation speed" for switchover to high/low speed.

The spindle position display provides two keys for clockwise and counterclockwise direction used during the first editing operation. The key makes the motor moving into the requested direction. A soft touch results in a defined STEP. Thus, new spindle positions can be edited under direct visual check of the operator with an accuracy of $\pm 1/100$ mm. Shaft position parameters once set can be filed as profile in the control. The serial interface enables network of maximum 32 spindle position displays with PC or PLC.

27/11/2018 Subject to modification in technic and design. Errors and omissions excepted.


Spindle position displays

Through hollow shaft up to ø14 mm, automated format adjustment Display LCD two lines, interface RS485

N 152

Terminal assignment SPA - connector, 4-pin Motor connector, 12-pin M8 connectorAssignment Connector Assignment Pin 1 Tx/Rx-, RS485 Pin A Pin 2 Tx/Rx+, RS485 Pin B Motor left Pin C Pin 3 Motor right Sensor supply +24 V Pin 4 Sensor supply 0 V Pin D Speed Pin E M8 connector Pin F Pin G Pin H Pin J Pin K Error signal Pin L Speed Pin M **GND** M16 male connector

Circuit diagram



27/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Spindle position displays

Through hollow shaft up to ø14 mm, automated format adjustment Display LCD two lines, interface RS485

N 152

Dimensions

