

Bellows coupling (D1=6 / D2=10)

For encoder with solid shaft

Article number: 11115159

Overview

- Bellows coupling free from backlash, including clamping hub
- High torsional resistance
- Compensation of shaft misalignments at minimized restoring force



Technical data


Technical data

Shaft diameter D1	6 mm
Shaft diameter D2	10 mm
Operating speed	≤15000 rpm
Operating temperature	-30...+120 °C
Moment of inertia	29 gcm ²
Torsional rigidity	1050 Nm/rad
Radial spring stiffness	11 N/mm


Technical data

Maximum torque	200 Ncm
Admissible axial movement	± 0.5 mm
Admissible parallel misalignment	± 0.25 mm
Admissible angular error	± 2 °
Weight approx.	33 g
Material	Bellows: stainless steel Hub: aluminium

Dimensions



Assembly drawing



a = Admissible axial movement
b = Admissible parallel misalignment
c = Admissible angular error