

**Overview**

- M12, female, A-coded, 3-poles; PUR, 2500 cm, shielded, free cable end
- Dragchain capable
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames, oils
- Halogen free



**Technical data**

Side A		Cable	
Head A: Connection	M12	Length tolerance	± 37.5 cm
Head A: Angle cable outlet	0°	Cable length	2500 cm
Head A: Gender	Female	Acceleration (C-track)	max. 5 m/s <sup>2</sup>
Head A: Coding	A	AWG	22
Head A: No. of poles	3	Bending radius (fixed)	min. 5 × outer diameter
Head A: LED	No	Torsion speed	max. 35 cycles/min
Head A: Width across flats	AF13	Bending radius (mobile)	min. 10 × outer diameter
Head A: Tightening torque	0.6 Nm	Cable type	3
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni	Cable weight	approx. 44 g/m
Head A: Body color	Black	Wire 1: Color	BN
Head A: Gasket material	FKM	Wire 2: Color	BK
Labeling sleeve side A	Yes	Wire 3: Color	BU
Side B		Conductor structure	42 × 0.1 mm
Head B: Connection	Open-ended wires	Cable diameter	5 mm ± 5%
Labeling sleeve side B	Yes	Conductor: Material	Copper, bare
Cables		External sheath: Material	PUR
Cable length	2500 cm	Insulation: Material	PP
Length tolerance	± 37.5 cm	Shielding: Material	Copper, tinned
Stripping length	20 mm	No. of bending cycles (C-track)	approx. 500000 Cycles
Shielded	Yes	Nominal voltage	300 V
Conductor structure	42 × 0.1 mm	No. of torsion cycles	approx. 200000 Cycles
AWG	22	Paired stranding	No
External sheath: Material	PUR	Single wire diameter	0.1 mm
External sheath: Color	Black	Cable: Test voltage	2 kV AC core-core ; 2 kV AC core-shield
Cable diameter	5 mm ± 5%	Torsion stress in °	± 30 °/m
Wire cross section	0.34 mm <sup>2</sup>	Total stranding	3 wires strand
Cable		Travel speed (C-track)	max. 3.3 m/s
Cable: Temperature range (mobile)	- 25 ...+ 80 °C	Traversing path (horizontal)	max. 5 m
Cable: Temperature range (fixed)	- 40 ...+ 80 °C	Wire cross section	0.34 mm <sup>2</sup>
Operating voltage (only UL listed)	30 V AC/DC	Wire processing	No
Shielded	Yes	Wire diameter incl. isolation	1.25 mm ± 5%
Shielding: Covering	approx. 80 %	External sheath: Color	Black
Bending radius (fixed)	25 mm	Electrical data	
Number of wires	3	Operating voltage	max. 60 V AC/DC
Number and diameter of wires	3x0,34	Operating voltage (only UL listed)	30 V AC/DC
		Nominal voltage	300 V
		Contact resistance	max. 30 mOhm

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

**Technical data**

**Electrical data**

Operating current per contact max. 4 A

**Mechanical data**

Head A: Degree of protection IP65, IP66K, IP67  
 Bending radius (mobile) min. 10 × outer diameter  
 Bending radius (fixed) min. 5 × outer diameter  
 No. of bending cycles (C-track) approx. 5000000 Cycles  
 Torsion speed max. 35 cycles/min  
 Torsion stress in ° ± 30 °/m  
 No. of torsion cycles approx. 2000000 Cycles  
 Acceleration (C-track) max. 5 m/s<sup>2</sup>  
 Travel speed (C-track) max. 3.3 m/s

**Environmental conditions**

Temperature range (mobile) - 25 ... + 80 °C  
 Temperature range (fixed) - 25 ... + 80 °C

**Environmental conditions**

Cable: Temperature range (fixed) - 40 ... + 80 °C  
 Dragchain capable Yes  
 Head A: Chemical resistance No  
 Head A: Flame resistance HB (UL 94)  
 Head A: Oil resistance ASTM 1 oil, mineral oils, limited to hydraulic oils  
 Head A: Acid and alkali resistant No  
 Head A: Pollution degree 3  
 Cable: Chemical resistance Good (DIN EN 60811-404)  
 Cable: Flame resistance Conform UL 1581 §1090 (H), CSA FT2, IEC 60332-2-2  
 Cable: Oil resistance Good (DIN EN 60811-404)  
 Cable: Silicone-free Yes

**Commercial data**

Eclass 27060311

**Side A**

**Technical drawing**




**Side B**


**Technical drawing**



**Coding**



**Connection diagram**



**Dimension drawing**

