

AFI4-###0.#0#4.1###

Overview

- All-in-One conductivity sensor
- All wetted parts in PEEK
- Compact, food-safe, hygienic design
- 3-A sanitary standards and FDA-compliant, EHEDG-certified
- HART® communication protocol





Technical date







Technical data	
Performance characteristic	s conductivity
Conductivity	14 selectable ranges
Min. measurable conductivity	50 μS/cm
Measuring ranges (selectable)	0 500 µS/cm 0 1 mS/cm 0 2 mS/cm 0 3 mS/cm 0 5 mS/cm 0 10 mS/cm 0 20 mS/cm 0 30 mS/cm 0 50 mS/cm 0 100 mS/cm 0 200 mS/cm 0 200 mS/cm 0 200 mS/cm 0 300 mS/cm 0 300 mS/cm 0 300 mS/cm
Max. measuring span	1000 mS/cm
Min. measuring span	500 μS/cm
Max. measuring error	± 1.0 % FSR , 0 1 mS/cm to 0 500 mS/cm ± 1.5 % FSR , 0 1000 mS/cm ± 1.5 % FSR , 0 500 μS/cm
Reference conditions for max. measuring error	Sensor incl. transmitter @ 25°C ambient temperature
Reference temperature	25 °C , adjustable
Repeatability	< 0.5 % FSR , > 1 mS/cm
Compensated temperature range	-20 150 °C
Temperature compensation	0.0 5.0 % FSR/K , adjustable
Step response time, T90	≤ 2.0 s
Sample time	≤ 0.4 s

s conductivity
≤ 0.1 % FSR/K
≤ 0.3 % FSR/K
s concentration
Programmable with FlexProgram
0 25 % by weight , HNO3 (nitric acid) 36 82 % by weight , HNO3 (nitric acid) 0 12 % by weight , NaOH (caustic soda) 25 50 % by weight , NaOH (caustic soda)
Customer defined (30 point lookup table)
s temperature
Free programmable range
-20 150 °C
≤ 15 s
± 1.5 K 0.3 K , 20 50 °C
Sensor incl. transmitter @ 25°C ambient temperature
≤ 0.05 % FSR/K

AFI4-###0.#0#4.1###

Technical data				
Process conditions		IO-Link interface		
Process temperature	-20 140 °C , permanent 140 150 °C , max. t < 1 h	Adjustable data (acyclic)	Measuring mode Sensor calibration	
Process pressure	≤ 25 bar		Media calibration Reference temperature	
SIP/CIP compatibility	< 60 min, @ medium temperature up to 150 °C		Temperature compensation Switch parameters	
Process connection		Dual Channel	Conductivity/Concentration	
Connection variants	G 1 A hygienic	Dual Channel 2	Temperature	
Immersion length	Refer to section "Dimensional drawings"	Dual Channel 3	Relay 1	
Wetted parts material	PEEK Natura	Dual Channel 4	Relay 2	
Surface roughness wetted parts	Ra ≤ 0.8 µm	Housing	·	
Ambient conditions		Style	FlexHousing, Ø80 mm	
Operating temperature range	-30 80 °C , with DFON touch screen -40 85 °C , without DFON touch screen		Bottom process connection Rear process connection	
Degree of protection (EN	IP67	Overall size	Refer to section "Dimensional drawings"	
60529)	IP69K , with appropriate cable	Material	AISI 304 (1.4301)	
Humidity	< 98 % RH , condensing	Electrical connection		
Insulation voltage	500 V AC	Connector (available for left	M12-A, 5-pin, stainless steel	
Vibration (sinusoidal) (EN 60068-2-6)	1.0 mm p-p (2 13.2 Hz), 0.7 g (13.2 100 Hz), 1 octave / min.	side)	M16x1.5, plastic M16x1.5, stainless steel M20x1.5, plastic	
Output signal			M20x1.5, stainless steel	
Conductivity/Concentration	4 20 mA 4 20 mA , + HART®	Connector (available for right side)	M16x1.5, plastic M16x1.5, stainless steel	
Temperature	4 20 mA	• ,	M20x1.5, plastic	
Relays	2 relays included in the display		M20x1.5, stainless steel	
Current rating	100 mA , max.		M12-A, 4-pin, stainless steel, 4 20 mA output	
Interface	IO-Link 1.1 With HART® modem		M12-A, 8-pin, stainless steel, 4 20 m + relay output	
HARTO! (f	With FlexProgrammer 9701	Power supply		
HART® interface Properties Universal commands		Voltage supply range	15 35 V DC 18 30 V DC , with IO-Link	
	Common-practice commands Conductivity device family commands	Current consumption (no load)	150 mA , max.	
	Device Specific Commands For more information please see ,HART Field Device Specification'	Power-up time	≤ 10 s , without DFON touch screen ≤ 16 s , with DFON touch screen	
Protocol	HCF standard, Rev.7	Factory settings		
IO-Link interface		HART®	Activated	
IO-Link version	1.1	IO-Link	Disabled	
Device profile	Smart Sensor Profile	Output mode	Conductivity	
IO-Link port type	Class A	Conductivity Range 1	0 200 mS/cm	
Baud rate	38,4 kbaud (COM2)	Conductivity Range 2	0 20 mS/cm	
Cycle time	≥ 8.4 ms	Conductivity Range 3	0 2 mS/cm	
Process data length	128 bit	Conductivity Range 4	0 500 μS/cm	
SIO-mode	Yes	Temperature output	0 150 °C	
Process data (cyclic)	Switch state	Output damping	0.00 s	
(-),	Signal analog output 1 Signal analog output 2	Temperature compensation Range 1-4	2.00 % FSR/K	
	Temperature	Output lower limit	3.70 mA	
	Unit temperature	Output upper limit	21.00 mA	
	Conductivity Concentration	Compliance and approvals		



AFI4-###0.#0#4.1###

Tech	ш	(Grai	 ĸІ	г.

Hygiene

Compliance and approvals

3-A (74-07)

EHEDG EL Class I FDA (21 CFR 177.2415)

Compliance and approvals

Safety cULus listed, E491206

Media group

Water

Media Ultra-pure water

Pure water

perating conditions					
Measuring range	Max. meas	uring error	Conductivity		
0 500 μS/cm	1,5 % FSR	7,5 μS/cm	55 nS/cm		
0 1 mS/cm	1,0 % FSR	10 μS/cm	1 μS/cm		
0 2 mS/cm	1,0 % FSR	20 μS/cm	10 μS/cm		
0 3 mS/cm	1,0 % FSR	30 μS/cm	600 µS/cm		
0 5 mS/cm	1,0 % FSR	50 μS/cm			
0 10 mS/cm	1,0 % FSR	100 μS/cm	1 mS/cm		
0 20 mS/cm	1,0 % FSR	200 μS/cm	i ilio/cili	AFIX	
0 30 mS/cm	1,0 % FSR	300 μS/cm		range	
0 50 mS/cm	1,0 % FSR	500 μS/cm	10 mS/cm	range	
0 100 mS/cm	1,0 % FSR	1 mS/cm	100 mS/cm		
0 200 mS/cm	1,0 % FSR	2 mS/cm	1000 mS/cm		
0 300 mS/cm	1,0 % FSR	3 mS/cm			
0 500 mS/cm	1,0 % FSR	5 mS/cm	_		
0 4000 0/	4 5 0/ 500	45 04			

0 2 mS/cm	1,0 % FSR	20 μS/cm	10 μS/cm			Process water
0 3 mS/cm	1,0 % FSR	30 μS/cm	600 µS/cm			Drinking water
0 5 mS/cm	1,0 % FSR	50 μS/cm				Beer
0 10 mS/cm	1,0 % FSR	100 μS/cm	1 mS/cm		Food & Beverage	Milk
0 20 mS/cm	1,0 % FSR	200 μS/cm	11113/0111	AFIX		Orange juice
0 30 mS/cm	1,0 % FSR	300 μS/cm		range		Apple juice
0 50 mS/cm	1,0 % FSR	500 μS/cm	10 mS/cm	range		Phosphoric acid
0 100 mS/cm	1,0 % FSR	1 mS/cm	100 mS/cm		Process	Hydrochloric acid
0 200 mS/cm	1,0 % FSR	2 mS/cm	1000 mS/cm			Sodium hydroxide
0 300 mS/cm	1,0 % FSR	3 mS/cm	-	-		
0 500 mS/cm	1,0 % FSR	5 mS/cm				
0 1000 mS/cm	1,5 % FSR	15 mS/cm				
Display						

General information	
Panel type	FSTN Graphical LCD
Display range	-9999 99999
Max. digit height	22 mm
Material	Polycarbonate
Ambient conditions	
Operating temperature range	-30 80 °C
Optimal readability temperature range	-10 70 °C
Degree of protection (EN 60529)	IP 67 IP 69 K
Input signal	
Input signal from transmit- ter	Digital, 2-way for communication between transmitter and display
Update time	≤1 s , max. 0.3 s , typ.

User configurable data	
Error- / Warning-indication	Individually configurable display and backlight indication in white, green or red colour, steady or flashing light. Configurable limits over the range
Media description	Customer programmable e.g. "MILK", "Water", "NaOH"
Measuring unit	μS/cm mS/cm % °C °F
User defined measuring unit	8 × 20 pixel matrix
Relays	
Contacts	2 x solid state relays
Max. load current	75 mA

Relays	
Contacts	2 x solid state relays
Max. load current	75 mA
Max. switching voltage	60 V


AFI4-###0.#0#4.1###




Selectable display views

Conductivity value with medium and additional values

Medium with additional values




Bar chart with additional values and medium




Concentration with additional values and medium



Conductivity value with measuring point (TAG)



Medium with measuring point (TAG)



Bar chart including temperature



Conductivity and concentration value



White background



Green background



Red background




Exemplary error message

Dimensional drawings (mm)


Housing



FlexHousing, available with or without DFON tochscreen



FlexHousing with bottom process connection





FlexHousing with rear process connection


AFI4-###0.#0#4.1###

Dimensional drawings (mm)

Process connection








G 1 A hygienic (BCID: A04), PEEK, 37 mm

G 1 A hygienic (BCID: A04), PEEK, 60 mm


G 1 A hygienic (BCID: A04), PEEK, 83 mm



Sensor tip with integrated Pt100 sensor element



AFI4-###0.#0#4.1###



Left side connection (front view): M12-A, 5-pin					
Function			Pin assignment		
+Vs	Power supply +	15 35 V DC	1		
GND (0 V)	Power supply -	15 35 V DC	3		
lout1+	Conductivity +	4 20 mA	4		
lout-	Conductivity -	4 20 mA	2		
IO-Link	IO-Link / SW		5		

lout- is internally connected as common for both Conductivity/Concentration and Temperature output.

Left side connection (front view): Cable gland				
Function			Recommended wiring	
+Vs	Power supply +	15 35 V DC	BN	
GND (0 V)	Power supply -	15 35 V DC	BU	
lout1+	Conductivity +	4 20 mA	BK	
lout-	Conductivity -	4 20 mA	WH	
IO-Link	IO-Link / SW		GY	

lout- is internally connected as common for both Conductivity/Concentration and Temperature output.

Right side connection (front view): M12-A, 4-pin					
Function			Pin assignment		
lout2+	Temperature +	4 20 mA	4		
lout-	Temperature -	4 20 mA	2		
S1	External input	n.c. / 24 V DC	1		
S2	External input	n.c. / 24 V DC	3		

lout- is internally connected as common for both Conductivity/Concentration and Temperature output.

Right side connection (front view): M12-A, 8-pin											
Function			Pin assignment								
lout2+	Temperature +	4 20 mA	2								
lout-	Temperature -	4 20 mA	7								
S1	External input	n.c. / 24 V DC	1								
S2	External input	n.c. / 24 V DC	8								
R11	Relay 1		5								
R12	Relay 1		6								
R21	Relay 2		3								
R22	Relay 2		4								

lout- is internally connected as common for both Conductivity/Concentration and Temperature output.

Right side connection (front view): Cable gland										
Function			Recommended wiring							
lout2+	Temperature +	4 20 mA	BN							
lout-	Temperature -	4 20 mA	BU							
S1	External input	n.c. / 24 V DC	WH							
S2	External input	n.c. / 24 V DC	RD							
R11	Relay 1		GY							
R12	Relay 1		PK							
R21	Relay 2		GN							
R22	Relay 2		YE							

lout- is internally connected as common for both Conductivity/Concentration and Temperature output.




AFI4-###0.#0#4.1###

Electrical connection

Terminal assignment transmitter


Terminal assignment DFON display





The ground connection is to be connected with the cable shield if using cable gland and shielded cable.

Equivalent circuit diagram





AFI4-###0.#0#4.1###

Ordering key - Configuration possibilities see website														
Ordering key - Configuration possibilities see website	AFI	4	- #	#	#	0		#	0	#	4	1	#	#
Product	A11	7	- #	7	#	Ü	•	π	٠	π	-	•	"	π
	AFI													
Туре														
Compact version		4												
Housing														
Bottom process connection			5											
Rear process connection			6											
Electrical connection														
2 x M16x1.5 cable gland				8										
1 x M16x1.5 + 1 x M20x1.5 cable gland				Α										
2 x M20x1.5 cable gland				В										
1 x M12-A, 5-pin + 1 x M12-A, 4-pin				С										
1 x M12-A, 5-pin + 1 x M12-A, 8-pin				D										
Material of el. connection														
Plastic					1									
Stainless steel, AISI 304 (1.4301)					3									
Cable length (cm)														
No cable, compact version						0								
Display														
Without display								1						
With display, with activated relays								4						
Safety														
Standard									0					
Configuration														
No configuration										0				
Configuration of range										1				
Configuration of range + display incl. 2 relays										3				
Output														
2 x 420 mA, HART											4			
Version														
IO-Link												1		
Process connection														
G 1 A hygienic, PEEK, length: 37 mm. (A04)													1	
G 1 A hygienic, PEEK, length: 83 mm. (A04)													2	
G 1 A hygienic, PEEK, length: 60 mm. (A04)													3	
Approvals														
Standard approvals														0
3-A / EHEDG														1
Calibration certificate														
No														
Calibration certificate, conductivity (5 points)														
Calibration certificate, temperature. (3 points)														
Calibration certificate, conductivity (5 points)														
and temperature (3 points)														