


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product	Conductivity transmitter / Graphical display
Name and address of the applicant	BAUMER A/S Runetoften 19 Arhus, 8210 Denmark
Name and address of the manufacturer	BAUMER A/S Runetoften 19 Arhus, 8210 Denmark
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	BAUMER A/S Runetoften 19 Arhus, 8210 Denmark  <input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	CombiLyz AFI4 & AFI5: 15-35 Vdc supply. For IO-Link variants:18-30Vdc DFON: 4.5-6.5 Vdc
Trademark / Brand (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	CombiLyz AFI4, CombiLyz AFI5, CombiView type DFON
Additional information (if necessary may also be reported on page 2)	National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010, IEC 61010-2-201:2017
As shown in the Test Report Ref. No. which forms part of this Certificate	E491206-D1000-2/A0/C0-CB issued on 2020-03-13

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA  
 UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK  
 UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN  
 UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-03-20

Signature:

Jan-Erik Storgaard