

## Bellows coupling (D1=06 / D2=08)

For encoder with solid shaft

Article number: 11261564

### Overview

- Backlash-free angle-synchronous transmission
- Optimum compensation of misalignments
- Very high torsional spring stiffness
- Small restoring force
- Vibration damping
- Stainless steel bellows



### Technical data


#### Technical data

Shaft diameter D1	6 mm
Shaft diameter D2	8 mm
Operating speed	≤10000 rpm
Operating temperature	-40...+140 °C
Moment of inertia	31 gcm <sup>2</sup>
Torsional rigidity	183 Nm/rad
Radial spring stiffness	17.8 N/mm


#### Technical data

Maximum torque	200 Ncm
Admissible axial movement	± 0.45 mm
Admissible parallel misalignment	± 0.35 mm
Admissible angular error	± 4 °
Weight approx.	22 g
Material	Bellows: stainless steel Flange: Aluminium, anodised

### Dimensions



### Assembly drawing



a = Admissible axial movement  
b = Admissible parallel misalignment  
c = Admissible angular error