


**Overview**

- Side A: Wires with Crimp contacts; Side B: Wires with Crimp contacts and shielding with Crimp contacts
- Cable structure: 5 x 0,34 mm<sup>2</sup>
- TPE; suitable for Food & Beverage
- Good resistance against chemicals and UV
- Halogen free



**Technical data**

**Side A**

Side A: Shielding length	72 mm
Side A: Shielding processing	Not processed
Side A: Crimp terminal wire 1	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 2	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 3	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 4	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 5	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated

**Side B**

Side B: Shielding length	100 mm
Side B: Shielding processing	Twisted and reduced to 0.34 mm <sup>2</sup>
Side B: Shielding crimp terminal	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 1	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 2	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 3	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated

**Side B**

Side B: Crimp terminal wire 4	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 5	0.34 mm <sup>2</sup> ; contact length: 6 mm; isolated

**Cables**

Cable length	500 cm
Length tolerance	± 7.5 cm
No. of wires	5
Shielded	Yes
External sheath: Material	TPE
External sheath: Color	Black
Cable diameter	6.2 mm
Wire cross section	0.34 mm <sup>2</sup>

**Electrical data**

Operating voltage (only UL listed)	30 V AC/DC
------------------------------------	------------

**Mechanical data**

Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 4 × outer diameter

**Environmental conditions**

Cable: Temperature range (fixed)	- 50 ...+ 90 °C
Cable: Chemical resistance	ECOLAB material resistance test passed

**Dimension drawing**

