


Overview

- M12, female, A-coded; 3-poles; TPE-S, 300 cm, shielded, free cable end
- Dragchain capable; suitable for robotics $\pm 180^\circ/m$; suitable for food & beverage
- Head A: IP65, IP68, IP69K
- ECOLAB tested
- Halogen free



Technical data

Side A		Cable	
Head A: Connection	M12	Number and diameter of wires	3x0,34
Head A: Angle cable outlet	0°	Length tolerance	+ 10 cm
Head A: Gender	Female	Cable length	300 cm
Head A: Coding	A	Acceleration (C-track)	max. 10 m/s ²
Head A: No. of poles	3	AWG	22
Head A: LED	No	Bending radius (fixed)	min. 5 × outer diameter
Head A: Width across flats	AF14	Torsion speed	max. 35 cycles/min
Head A: Tightening torque	0.6 Nm	Bending radius (mobile)	min. 10 × outer diameter
Head A: Knurled nut material	Stainless steel (V4A)	Cable weight	approx. 37.4 g/m
Head A: Body color	Blue	Wire 1: Color	BN
Head A: Gasket material	EPDM	Wire 2: Color	BK
Labeling sleeve side A	No	Wire 3: Color	BU
Side B		Conductor structure	42 × 0.1 mm
Head B: Connection	Open-ended wires	Cable diameter	5.2 mm ± 5%
Labeling sleeve side B	No	Conductor: Material	Copper, bare
Cables		External sheath: Material	TPE-S
Cable length	300 cm	Insulation: Material	PP
Length tolerance	+ 10 cm	Shielding: Material	Copper, tinned
Stripping length	20 mm	No. of bending cycles (C-track)	approx. 4000000 Cycles
Shielded	Yes	Nominal voltage	300 V AC
Conductor structure	42 × 0.1 mm	No. of torsion cycles	approx. 2000000 Cycles
AWG	22	Paired stranding	No
External sheath: Material	TPE-S	Single wire diameter	0.1 mm
External sheath: Color	Blue	Cable: Test voltage	3 kV
Cable diameter	5.2 mm ± 5%	Torsion stress in °	± 180 °/m
Wire cross section	0.34 mm ²	Total stranding	3 wires strand
Cable		Travel speed (C-track)	max. 3 m/s
Cable: Temperature range (mobile)	- 25 ...+ 105 °C	Traversing path (horizontal)	max. 10 m
Cable: Temperature range (fixed)	- 40 ...+ 105 °C	Wire cross section	0.34 mm ²
Operating voltage (only UL listed)	30 V AC/DC	Wire processing	No
Shielded	Yes	Wire diameter incl. isolation	1.27 mm ± 5%
Shielding: Covering	approx. 85 %	External sheath: Color	Blue
Bending radius (fixed)	26 mm	Electrical data	
Number of wires	3	Operating voltage	max. 60 V AC/DC
		Operating voltage (only UL listed)	30 V AC/DC

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change. 2023-10-09

Technical data

Electrical data

Nominal voltage	300 V AC
Contact resistance	max. 30 mOhm
Operating current per contact	max. 4 A

Mechanical data

Head A: Degree of protection	IP65, IP68, IP69K
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter
No. of bending cycles (C-track)	approx. 4000000 Cycles
Torsion speed	max. 35 cycles/min
Torsion stress in °	± 180 °/m
No. of torsion cycles	approx. 2000000 Cycles
Acceleration (C-track)	max. 10 m/s ²
Travel speed (C-track)	max. 3 m/s

Environmental conditions

Temperature range (mobile)	- 25 ...+ 105 °C
Temperature range (fixed)	- 40 ...+ 105 °C

Environmental conditions


Cable: Temperature range (fixed)	- 40 ...+ 105 °C
Dragchain capable	Yes
Head A: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	ASTM 1 oil, mineral oils, limited to hydraulic oils
Head A: Acid and alkali resistant	ECOLAB tested
Head A: Pollution degree	3
Cable: Chemical resistance	ECOLAB material resistance test passed
Cable: Acid and alkali resistant	Good (FDA 21 178.3620, 178.3297, 177.1520, EU 10/2011)
Cable: Silicone-free	Yes

Commercial data

Eclass	27060311
--------	----------


Side A

Technical drawing




Side A

Coding




Side B

Technical drawing



Connection diagram



Dimension drawing

