

Overview

- Female straight
- M12 , 5-pole, A-coded
- max. 0,75mm², 6 - 8mm, shielded



Technical data

Side A

Head A: Connection	M12
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Coding	A
Head A: Shielded	Yes
Head A: No. of poles	5
Head A: Tightening torque	0.6 Nm
Head A: Knurled nut material	GD-Zn,Ni
Head A: Gasket material	Elastomer
Max. AWG	20
Connection method	Screw terminals
Wire cross section (max.)	0.75 mm ²

Side A

Cable diameter (max.)	8 mm
Cable diameter (min.)	6 mm

Electrical data

Operating voltage	max. 50 V AC/DC
Operating current per contact	max. 4 A

Mechanical data

Head A: Degree of protection	IP67
------------------------------	------

Environmental conditions


Head A: Pollution degree	3
--------------------------	---

Commercial data

Eclass	27440102
--------	----------


Side A

Technical drawing



Side A

Coding



Connection diagram

