

overview

- Gigabit Ethernet interface cable
- CAT5e
- RJ45 (screw lock) to RJ45
- suitable for cable carrier and torsion applications
- length 10,0 m



technical data

electrical data

number of poles	8
connectors	RJ45, screw lock RJ45

mechanical data

bending radius static	42 mm
bending cycles	10000000
use in cable carriers	yes

mechanical data

cable length [m]	10 m
weight	≤ 800 g
material	PVC, lead-free


interface

data interface	GigE
----------------	------

environmental conditions

flame resistance	UL20276 80°C / 30V
------------------	--------------------

pin assignment



RJ45S RJ45

1:	1
2:	2
3:	3
4:	4

RJ45S RJ45

5:	5
6:	6
7:	7
8:	8