


**Overview**

- M12, female, A-coded, 5-poles; PVC, 2500 cm, open cable end
- Head A: IP65, IP66K, IP67



**Technical data**

Side A		Cable	
Head A: Connection	M12	Number of wires	5
Head A: Angle cable outlet	0°	Number and diameter of wires	5x0,34
Head A: Gender	Female	Cable length	2500 cm
Head A: Coding	A	AWG	22
Head A: No. of poles	5	Bending radius (fixed)	min. 5 × outer diameter
Head A: LED	No	Bending radius (mobile)	min. 10 × outer diameter
Head A: Width across flats	AF13	Cable type	1
Head A: Tightening torque	0.6 Nm	Wire 1: Color	BN
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni	Wire 2: Color	BK
Head A: Body color	Black	Wire 3: Color	BU
Head A: Gasket material	FKM	Wire 4: Color	WH
Labeling sleeve side A	Yes	Wire 5: Color	GY
Side B		Conductor structure	19 × 0.15 mm
Head B: Connection	Open-ended wires	Cable diameter	5.2 mm ± 5%
Labeling sleeve side B	Yes	Conductor: Material	Copper, bare
Cables		External sheath: Material	PVC
Cable length	2500 cm	Insulation: Material	PVC
Shielded	No	Nominal voltage	300 V AC
Conductor structure	19 × 0.15 mm	Paired stranding	No
AWG	22	Single wire diameter	0.15 mm
External sheath: Material	PVC	Cable: Test voltage	2 kV
External sheath: Color	Gray	Total stranding	5 wires strand around core-filler
Cable diameter	5.2 mm ± 5%	Wire cross section	0.34 mm <sup>2</sup>
Wire cross section	0.34 mm <sup>2</sup>	Wire processing	No
Cable		Wire diameter incl. isolation	1.25 mm ± 5%
Cable: Temperature range (mobile)	- 5 ...+ 80 °C	External sheath: Color	Gray
Cable: Temperature range (fixed)	- 30 ...+ 80 °C	Electrical data	
Shielded	No	Operating voltage	max. 125 V AC/DC 0
		Nominal voltage	300 V AC

**Technical data**
**Electrical data**

Contact resistance	max. 30 mOhm
Operating current per contact	max. 4 A

**Mechanical data**

Head A: Degree of protection	IP65, IP66K, IP67
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter

**Environmental conditions**

Temperature range (mobile)	- 5 ...+ 80 °C
Temperature range (fixed)	- 25 ...+ 80 °C
Cable: Temperature range (fixed)	- 30 ...+ 80 °C
Dragchain capable	No
Head A: Chemical resistance	No

**Environmental conditions**

Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.
Head A: Acid and alkali resistant	No
Head A: Pollution degree	3
Cable: Chemical resistance	Good
Cable: Flame resistance	Conform UL 1581 VW-1
Cable: Oil resistance	Good
Cable: Silicone-free	Yes

**Commercial data**

Eclass	27060311
--------	----------