


**Overview**

- M12, female, A-coded, 8-poles; PUR, 200 cm, shielded, free cable end
- Head A: IP67
- Cable: Twisted pairs, halogen free



**Technical data**

Side A		Cables	
Head A: Connection	M12	Stripping length	60 mm
Head A: Angle cable outlet	0°	Shielded	Yes
Head A: Gender	Female	Conductor structure	18 × 0.10 mm
Head A: Coding	A	AWG	26
Head A: No. of poles	8	External sheath: Material	PUR
Head A: LED	No	External sheath: Color	Black
Head A: Width across flats	AF18	Cable diameter	6.0 mm ± 5%
Head A: Tightening torque	0.6 Nm	Wire cross section	0.14 mm <sup>2</sup>
Head A: Knurled nut material	CuZn,Ni	Cable	
Labeling sleeve side A	No	External sheath: Shore hardness	0 0
Side B		Operating voltage (only UL listed)	30 V
Head B: Connection	Open-ended wires	Power over ethernet (only UL listed)	2 A
Side B: Stripping length wire 1	10 mm	Cable diameter tolerance	Ø 6.0 ± 0.3 mm
Side B: Stripping length wire 2	10 mm	Weight [conductor]	42 g/m
Side B: Stripping length wire 3	10 mm	Shielded	Yes
Side B: Stripping length wire 4	10 mm	Shielding: Covering	85 %
Side B: Stripping length wire 5	10 mm	Bending radius (fixed)	45 mm
Side B: Stripping length wire 6	10 mm	Number of wires	8
Side B: Stripping length wire 7	10 mm	Cable length	200 cm
Side B: Stripping length wire 8	10 mm	AWG	26
Labeling sleeve side B	No	Wire 1: Color	WH
Cables		Wire 2: Color	BN
Cable length	200 cm	Wire 3: Color	GN
		Wire 4: Color	YE
		Wire 5: Color	GY
		Wire 6: Color	PK
		Wire 7: Color	BU
		Wire 8: Color	RD

**Technical data**

Cable	
Conductor structure	18 × 0.10 mm
Cable diameter	6.0 mm ± 5%
Insulation resistance	min. 0.2 MOhm x m
External sheath: Material	PUR
Insulation: Material	TPE
Shielding: Material	Copper, tinned
Operating current per wire	1.5 A
Paired stranding	Yes
Paired stranding info	(WH, BN); (GN, YE); (GY, PK); (BU, RD)
Single wire diameter	0.1 mm
Cable: Test voltage	2 kV 0
Wire cross section	0.14 mm <sup>2</sup>
Wire stripping length	10 mm
Wire diameter incl. isolation	0.9 mm ± 5%
External sheath: Color	Black

**Electrical data**

Operating voltage	max. 30 V AC 0
Operating voltage (only UL listed)	30 V
Operating current per contact	max. 1.5 A

**Mechanical data**


Head A: Degree of protection	IP67
------------------------------	------

**Environmental conditions**


Temperature range (mobile)	-40 ... + 90 °C
Temperature range (fixed)	-50 ... + 90 °C
Dragchain capable	No
Head A: Pollution degree	3

**Side A**

**Coding**




**Connection diagram**



**Side B**

**Technical drawing**



**Dimension drawing**

