

# FSE 025B2001

Glass fiber optic cable

Article number: 10258994

## Overview

- Through-beam type
- Actual range up to 140 mm
- Cylindrical smooth sensing head  $\varnothing 3$  mm
- Plastic jacket 25 cm long
- Operating temperature up to +70 °C
- For rugged fiber optic sensors FVDM 15



Picture similar

## Technical data


### General data

Operating principle	Through-beam type
Actual range Sb	140 mm
Fiber optic head	Cylindrical smooth
Operating temperature	-25 ... +70 °C
Exit angle	60°
Fiber optics can be shortened to length	No
Integrated lens	No
Adaptable lens	No
Infrared light compatibility (1450 nm)	Yes
Smallest object recognizable	0.1 mm

### Mechanical data

Width / diameter (head)	3 mm
Height / length (head)	17 mm
Material (head)	Aluminum
Bending radius (fixed)	7.5 mm
Bending radius (mobile)	15 mm
Cable jacket diameter	2.5 mm
Material cable jacket	PVC
Fiber cross section	1 mm <sup>2</sup>
Material (fiber optic cable)	Glass
Length (fiber optic cable)	25 cm

## Dimension drawing



**FSE 025B2001**

Glass fiber optic cable

Article number: 10258994

**Accessories****Fitting fiber optic sensors**

10234639	FVDM 15N5103
10122368	FVDM 15N5103/S14
10234520	FVDM 15P5103
10239451	FVDM 15P5103/S14
10234519	FVDM 15P5130
10124952	FVDM 15P5130/S14

**Mounting accessories**

10103230	Cap nut (replace) for fiber optics series 15
----------	--