

Overview

- M16, Female, A-coded, 7-poles;
- Spiral cable, min. 150 cm max. 1260 cm, free cable end
- Outer winding diameter 19 mm
- For mobile applications
- Head A: IP67
- Cable: good resistance against chemicals, flames, oils



Technical data

Side A

Head A: Connection	M16
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: No. of poles	7
Head A: LED	No
Head A: Width across flats	SW 24
Head A: Knurled nut material	CuZn

Side B

Head B: Connection	Open-ended wires
--------------------	------------------

Cables

Cable length	150 cm
Length tolerance	+ 10 cm
Stripping length	20 mm
Shielded	Yes
Conductor structure	18 × 0.1 mm
AWG	26
External sheath: Material	PUR
External sheath: Color	Black
Cable diameter	5.3 mm ± 5%
Wire cross section	0.14 mm ²

Electrical data

Operating voltage (only UL listed)	350 V
Nominal voltage	300 V
Operating current per contact	max. 1.5 A

Mechanical data


Head A: Degree of protection	IP67
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter
No. of bending cycles (C-track)	approx. 500000 Cycles
Torsion stress in °	± 180 °/m
No. of torsion cycles	approx. 500000 Cycles

Environmental conditions

Temperature range (mobile)	- 25 ...+ 80 °C
Temperature range (fixed)	- 25 ...+ 80 °C
Cable: Chemical resistance	Good (DIN EN 60811-404)
Cable: Oil resistance	Good (DIN EN 60811-404)


Side A

Technical drawing



Side A

Coding



Side B

Technical drawing

