

**Overview**

- 2 mm
- NPN break function (NC)
- connector M8
- -25 ... 75 °C
- IP 67



Picture similar



**Technical data**


General data		Electrical data	
Mounting type	Flush	Short circuit protection	Yes
Nominal sensing distance Sn	2 mm	Reverse polarity protection	Yes
Hysteresis	3 ... 20 % of Sr	Mechanical data	
Output indicator	LED red	Type	Rectangular
Electrical data		Material (sensing face)	PBT
Switching frequency	5 kHz	Housing material	Die-cast zinc nickel plated
Voltage supply range +Vs	6 ... 36 VDC	Dimension	8 mm
Current consumption max. (no load)	12 mA	Housing length	45.9 mm
Output circuit	NPN break function (NC)	Connection types	Connector M8
Voltage drop Vd	< 2 VDC	Ambient conditions	
Output current	< 200 mA	Operating temperature	-25 ... +75 °C
		Protection class	IP 67

# IFFM 08N37A1/O1S35L

Inductive proximity switch - miniature

Article number: 10159800

## Dimension drawing



## Connection diagram

