

## CFAM 12P1600/S14

Capacitive proximity sensors

Article number: 10236345

### Overview

- 4 mm
- PNP make function (NO)
- potentiometer, 240°
- connector M12
- -25 ... 75 °C
- IP 65



Picture similar



### Technical data

#### General data

Nominal sensing distance Sn	4 mm
Nominal sensing distance Sn adjustable	0.5 ... 4 mm
Mounting type	Flush
GND electrode	Yes
Temperature drift	± 15 % (+10 ... +70 °C)
Sensitivity adjustment	Potentiometer, 240°
Output indicator	LED yellow
Measurement type	Contactless

#### Field of application

Detection of non-conductive media	Yes
Fill level detection through container	Yes
Liquids in direct contact	No
Object detection / bulk goods	Yes

#### Electrical data

Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	20 mA
Output circuit	PNP make function (NO)
Output current	< 200 mA
Voltage drop Vd	< 1.5 VDC
Switching frequency	50 Hz
Short circuit protection	Yes
Reverse polarity protection	Yes

#### Mechanical data

Type	Cylindrical threaded
Housing material	Brass nickel plated
Dimension	12 mm
Housing length	76 mm
Connection types	Connector M12

#### Ambient conditions


Operating temperature	-25 ... +75 °C
Protection class	IP 65

# CFAM 12P1600/S14

Capacitive proximity sensors

Article number: 10236345

## Dimension drawing



## Connection diagram

