


CFBM 20P3600

Capacitive proximity sensors

Article number: 10119697

Overview

- 10 mm
- PNP break function (NC)
- potentiometer, 18 turn
- cable, 2 m
- -25 ... 75 °C
- IP 65



Picture similar



Technical data

General data

| | |
|--|-------------------------|
| Nominal sensing distance Sn | 10 mm |
| Nominal sensing distance Sn adjustable | 2 ... 10 mm |
| Mounting type | Flush |
| GND electrode | Yes |
| Temperature drift | ± 15 % (+10 ... +70 °C) |
| Sensitivity adjustment | Potentiometer, 18 turn |
| Output indicator | LED yellow |
| Measurement type | Contactless |

Field of application

| | |
|--|-----|
| Detection of non-conductive media | Yes |
| Fill level detection through container | Yes |
| Liquids in direct contact | No |
| Object detection / bulk goods | Yes |

Electrical data

| | |
|------------------------------------|-------------------------|
| Voltage supply range +Vs | 10 ... 30 VDC |
| Current consumption max. (no load) | 20 mA |
| Output circuit | PNP break function (NC) |
| Output current | < 200 mA |
| Voltage drop Vd | < 2.5 VDC |
| Switching frequency | 50 Hz |
| Short circuit protection | Yes |
| Reverse polarity protection | Yes |

Mechanical data

| | |
|------------------|---------------------|
| Type | Cylindrical smooth |
| Housing material | Brass nickel plated |
| Dimension | 20 mm |
| Housing length | 79.5 mm |
| Connection types | Cable, L=2 m |

Ambient conditions


| | |
|-----------------------|----------------|
| Operating temperature | -25 ... +75 °C |
| Protection class | IP 65 |

Remarks

- EMC: EN 60947-5-2:2007+A1:2012

CFBM 20P3600

Dimension drawing



Connection diagram

