



features

- Gigabit Ethernet interface cable
- CAT6
- M12/8-pin connector, X-coded (screw lock)
- cable carrier compatible
- length 20,0 m

mechanical data

material	PUR
bending radius (static)	51 mm
bending radius (moved installation)	51 mm
bending cycles	1000000
use in cable carriers	yes, flexible cable
cable length [m]	20 m
weight	≤ 1400 g

electrical data

transfer category	CAT6
number of poles	8
connectors	M12/x-coded, screw lock RJ45


interface

data interface	GigE
----------------	------

environmental conditions

flame resistance	IEC 60332-1-2 AWM 20963 / 80°C 30V
halogen-free	IEC 60754-1
operation temperature (static)	-40 ... +70 °C @ T = measurement point
protection class	IP 65/67/68 (camera side)

pin assignment



M12	RJ45	M12	RJ45
1:	1	7:	5
2:	2	8:	4
3:	3	5:	7
4:	6	6:	8