

LXG-120C

Dual GigE, 12 Megapixel, Color

Article number: 11117847

Overview

- 4096 × 3072 px
- ams (CMOSIS) CMV12000
- APS-C CMOS
- 19 fps
- Dual Gigabit Ethernet



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV12000
Mono/Color	Color
Color filter	RGB Bayer Mosaic
Sensor type	APS-C CMOS
Shutter type	Global shutter
Resolution	4096 × 3072 px
Pixel size	5.5 × 5.5 μm
Exposure time	0.04 ... 1000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 4096 × 3072 px, max. 19 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 4096 × 3072 px, max. 50 fps
Pixel formats	BayerGB8 BayerGB12 BayerGB12 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Raw Bayer
Color processing	NA

Camera features

Synchronization	free running trigger
-----------------	----------------------

Camera features

Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mb/Sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	54.25 mm
Weight	≤ 290 g (M58-mount)

LXG-120C

Dual GigE, 12 Megapixel, Color

Article number: 11117847

Technical data

Mechanical data

Material housing: aluminum

Electrical data

Voltage supply range +Vs 12 ... 24 V DC (external power supply)
36 ... 57 V DC (Power over Ethernet)

Power consumption approx. 7,0 W @ 24 VDC
approx. 6,5 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size 128 kB

Environmental conditions

Operating temperature +5 ... +66 °C @ T = measurement point

Humidity 10 ... 90 % (non-condensing)

Protection class IP 40

Conformity

Conformity CE
RoHS
EAC
BIS-CRS (R-41207004)

Dimension drawing

