


LXG-20M.PS

Gigabit Ethernet, 2 Megapixel, Monochrome

Article number: 11174305

Overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000 V3
- 2/3" CMOS
- 338 fps
- Gigabit Ethernet



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000 V3
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2048 × 1088 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.03 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	13.1 e-
Saturation capacity	10443 e-
Dynamic range	54.8 dB
Signal-to-noise ratio	40.2 dB
Quantum efficiency	50.2 % @ 536 nm

Acquisition formats

Image formats, interface	Full Frame, 2048 × 1088 px, max. 56 fps frame rate max.
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 338 fps
Pixel formats	Mono8 Mono10

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono
Image processing	VisualApplets 3.x

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins (2x)
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	54.25 mm

LXG-20M.PS

Gigabit Ethernet, 2 Megapixel, Monochrome

Article number: 11174305

Technical data

Mechanical data

Weight	≤ 340 g
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	Approx. 5.8 W @ 24 VDC Approx. 6.7 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +50 °C
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

