

**Overview**

- 2 mm
- PNP make function (NO)
- connector M8
- -25 ... 75 °C
- IP 67




Picture similar



**Technical data**

General data		Electrical data	
Mounting type	Flush	Short circuit protection	Yes
Nominal sensing distance S <sub>n</sub>	2 mm	Reverse polarity protection	Yes
Hysteresis	3 ... 20 % of S <sub>r</sub>	Mechanical data	
Output indicator	LED red	Type	Rectangular
Electrical data		Material (sensing face)	PBT
Switching frequency	5 kHz	Housing material	Die-cast zinc nickel plated
Voltage supply range +V <sub>s</sub>	6 ... 36 VDC	Dimension	8 mm
Current consumption max. (no load)	12 mA	Housing length	27.4 mm
Output circuit	PNP make function (NO)	Connection types	Connector M8
Voltage drop V <sub>d</sub>	< 2 VDC	Ambient conditions	
Output current	< 200 mA	Operating temperature	-25 ... +75 °C
		Protection class	IP 67

**Dimension drawing**



**Connection diagram**

