

LXG-250C

Dual GigE, 25 Megapixel, Color

Article number: 11150457

Overview

- 5120 × 5120 px
- Onsemi PYTHON 25K
- APS-H CMOS
- 9 fps
- Dual Gigabit Ethernet



GEN*i*CAM



Technical data

Sensor information

Sensor	onsemi PYTHON 25K
Mono/Color	Color
Color filter	RGB Bayer Mosaic
Sensor type	APS-H CMOS
Shutter type	Global shutter
Resolution	5120 × 5120 px
Pixel size	4.5 × 4.5 µm
Exposure time	0.03 ... 1000 ms

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5120 × 5120 px, max. 9 fps Binning 2×2, 2560 × 2560 px, max. 9 fps Binning 1×2, 5120 × 2560 px, max. 9 fps Binning 2×1, 2560 × 5120 px, max. 9 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5120 × 5120 px, max. 32 fps
Pixel formats	BayerGB8 BayerGB12 BayerGB12 Packed

Image preprocessing

Analog controls	Gain (0 ... 23,5 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Raw Bayer
Color processing	NA

Camera features

Synchronization	free running trigger
-----------------	----------------------

Camera features

Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mb/s/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	56.32 mm
Weight	≤ 320 g (M58-mount)

LXG-250C

Dual GigE, 25 Megapixel, Color

Article number: 11150457

Technical data

Mechanical data

Material housing: aluminum

Electrical data

Voltage supply range +Vs 12 ... 24 V DC (external power supply)
36 ... 57 V DC (Power over Ethernet)

Power consumption approx. 5,4 W @ 24 VDC (sequential readout)
approx. 7,6 W @ 48 VDC (PoE, sequential readout)

Non-volatile memory

Flash memory size 128 kB

Environmental conditions

Operating temperature +5 ... +68 °C @ T = measurement point

Humidity 10 ... 90 % (non-condensing)

Protection class IP 40

Conformity

Conformity CE
KC (R-REI-BkR-LXG-250M)
RoHS
EAC

Dimension drawing

