


Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing

Magnetic sensing, through hollow shaft max. $\varnothing 80$ mm, singleturn 8...17 Bit

Additional 1...131072 pulses or 1...8192 sinewave cycles per turn

MHAP 100 - HDmag



MHAP 100 - Version for axial screw mounting

Features

- Absolute encoder with magnetic sensing and without bearings
- Sensor head with integrated FPGA signal processing
- Absolute resolution max. 17 bit singleturn
- Additional incremental output
- Robust and wearless
- Electronics is fully encapsulated
- High protection
- Large tolerances: axial ± 1 mm, radial max. 0.5 mm
- Simple mounting, easy adaptation
- Several mounting possibilities

Technical data - electrical ratings

Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Approvals	CE, UL approval / E217823

Technical data - electrical ratings (SSI)

Voltage supply	4.5...30 VDC
Interface	SSI
Function	Singleturn
Steps per revolution	≤ 131072 / 17 bit
Sensing method	Magnetic
Code	Gray or binary
Code sequence	CW default
Additional outputs	Square-wave TTL (RS422) Square-wave universal HTL/ TTL SinCos

Technical data - electrical ratings (square-wave)

Voltage supply	4.5...30 VDC
Consumption w/o load	≤ 300 mA
Pulses per revolution	1...131072
Phase shift	$90^\circ \pm 10^\circ$
Duty cycle	40...60 %
Sensing method	Magnetic
Output frequency	≤ 2 MHz
Output signals	A+, A-, B+, B-
Output stages	HTL TTL/RS422

Technical data - electrical ratings (SinCos)

Voltage supply	4.5...30 VDC
Consumption w/o load	≤ 300 mA
Sinewave cycles per revolution	1...8192
Phase shift	$90^\circ \pm 5^\circ$
Sensing method	Magnetic
Output signals	A+, A-, B+, B-
Output stages	SinCos 1 Vpp
Difference of SinCos amplitude	≤ 20 mV
Harmonics typ.	-40 dB
DC offset	≤ 20 mV
Bandwidth	400 kHz (-3 dB)

Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing
Magnetic sensing, through hollow shaft max. ø80 mm, singleturn 8...17 Bit
Additional 1...131072 pulses or 1...8192 sinewave cycles per turn

MHAP 100 - HDmag

Technical data - mechanical design	
Sensor head	FPGA signal processing
Size (flange)	ø101.3 mm
Shaft type	ø16...80 mm (through hollow shaft)
Axial tolerance	±1 mm (wheel/head)
Radial tolerance	0.1...0.5 mm (wheel/head)
Protection DIN EN 60529	IP 67 (head), IP 68 (wheel)
Operating speed	≤8000 rpm
Materials	Housing sensing head: aluminium alloy Wheel: stainless steel (1.4104)
Operating temperature	-20...+85 °C
Resistance	IEC 60068-2-6 Vibration 30 g, 55-2000 Hz IEC 60068-2-27 Shock 300 g, 2 ms
Accuracy of magnetic measure	±400 "
Connection	Flange connector M23, 17-pin

Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing

Magnetic sensing, through hollow shaft max. $\varnothing 80$ mm, singleturn 8...17 Bit

Additional 1...131072 pulses or 1...8192 sinewave cycles per turn

MHAP 100 - HDmag

Part number

MHAP 100 B5

	S						D
--	---	--	--	--	--	--	---

Pulse number/sinewave cycles - see table

Voltage supply / signals

P 4.5...30 VDC / SinCos

R 4.5...30 VDC / square-wave (TTL)

U 5...30 VDC / square-wave (5 VDC = TTL / 10...30 VDC = HTL universal)

Z Without additional output signals

Parity bit

O Odd

E Even

N None

Resolution Singleturn (bit)

8, 9, 10, 11, 12, 13, 14, 15, 16, 17

Code

B Binary code

G Gray code

Mounting type / hollow shaft (\varnothing mm)

Screw or shrink fit mounting

G38, G45, G50, G55, G60, G65, G70, G75, G80

Clamping set mounting

Z16, Z20, Z22, Z25, Z28, Z32, Z35, Z38, Z40, Z42, Z45, Z48, Z50, Z55, Z60, Z63, Z65

Clamping ring mounting

K25, K30, K32, K38, K40, K45, K48, K50, K55, K56, K60, K65, K70, K75

Pulse number/sinewave cycles

1	16	256	4096	65536
2	32	512	8192	131072
4	64	1024	16384	
8	128	2048	32768	

Maximum sinewave cycles 8192 for SinCos output.


Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing
 Magnetic sensing, through hollow shaft max. $\varnothing 80$ mm, singleturn 8...17 Bit
 Additional 1...131072 pulses or 1...8192 sinewave cycles per turn


MHAP 100 - HDmag

Data transfer

Without parity bit



With parity bit




$$T = 0.5 \dots 10 \mu\text{s}$$

$$T_m = 15 \mu\text{s}$$


Taktfrequenz ≤ 2 MHz

Output signals

Version with additional square-wave signals
 HTL oder TTL at positive rotating direction



Version with additional SinCos signals
 at positive rotating direction




Terminal assignment

View A

Flange connector M23, 17-pin, male, CW

Pin	Assignment
1	Do not use
2	Do not use
3	Do not use
4	Do not use
5	Do not use
6	Do not use
7	+UB
8	SSI Clock+
9	SSI Clock-
10	\perp
11	Internal shield
12	B+ *
13	B- *
14	SSI Data+
15	A+ *
16	A- *
17	SSI Data-

* Do not use in version without incremental output



Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing


Magnetic sensing, through hollow shaft max. $\varnothing 80$ mm, singleturn 8...17 Bit

Additional 1...131072 pulses or 1...8192 sinewave cycles per turn


MHAP 100 - HDmag

Dimensions

Version for axial screw mounting or shrink fit mounting



Version for clamping set mounting



Encoders without bearings - absolute

Absolute encoder, sensor head with integrated FPGA signal processing
 Magnetic sensing, through hollow shaft max. $\varnothing 80$ mm, singleturn 8...17 Bit
 Additional 1...131072 pulses or 1...8192 sinewave cycles per turn

MHAP 100 - HDmag

Dimensions

Version for clamping ring mounting

