


MXGC20

Gigabit Ethernet, 2 Megapixel, Monochrome

Article number: 11094942

Overview

- 2040 × 1084 px
- ams (CMOSIS) CMV2000
- 2/3" CMOS
- 55 fps
- Gigabit Ethernet



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2040 × 1084 px
Pixel size	5.5 × 5.5 μm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2040 × 1084 px, max. 55 fps
Pixel formats	Mono8 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 18 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
Sequencer	Automated control for series of images using different sets of parameters

Camera features

Sequencer parameter	Exposure time gain factor output line ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	120 MB

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45)
Process interface	JSTBM08B-SRSS-TB 8 pins
Power supply	JSTBM03B-SRSS-TB 3 pins

Mechanical data

Lens mount	C-mount / S-mount (adapter)
Width	28.5 mm (sensor print) 48 mm (system print)
Height	28.5 mm (sensor print) 48 mm (system print)
Weight	≤ 30 g
Material	without housing

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

MXGC20

Gigabit Ethernet, 2 Megapixel, Monochrome

Article number: 11094942

Technical data

Electrical data

Power consumption	Approx. 3.5 W @ 12 VDC and 55.0 fps Approx. 3.8 W @ 48 VDC (PoE) and 55.0 fps
-------------------	--

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	Depends on the thermal encapsulation ($T_{max} = 70\text{ °C}$ @ Measurement Point)
-----------------------	---

Environmental conditions

Humidity	10 ... 90 % (non-condensing)
----------	------------------------------

Digital I/Os

Lines	1 input line 3 output lines
-------	--------------------------------

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

