

Overview

- 0,8 mm
- NPN make function (NO)
- flylead connector M8
- -25 ... 75 °C
- IP 67




Picture similar



Technical data

General data		Electrical data	
Mounting type	Flush	Short circuit protection	Yes
Nominal sensing distance S _n	0.8 mm	Reverse polarity protection	Yes
Hysteresis	2 ... 20 % of S _r	Mechanical data	
Output indicator	LED red	Type	Cylindrical threaded
Electrical data		Material (sensing face)	POM
Switching frequency	3 kHz	Housing material	Stainless steel
Voltage supply range +V _s	6 ... 30 VDC	Dimension	4 mm
Current consumption max. (no load)	12 mA	Housing length	22 mm
Output circuit	NPN make function (NO)	Connection types	Flylead connector M8
Voltage drop V _d	< 2 VDC	Tightening torque max.	1.8 Nm (Front: 1,2 Nm)
Output current	< 100 mA	Ambient conditions	
		Operating temperature	-25 ... +75 °C
		Protection class	IP 67

Dimension drawing



- Standard cable length 200 mm (L)

Connection diagram

