

O200.ER-GW1J.72CV/E026_H006

Through beam sensors - miniature

Article number: 11230904

Overview

- Most secure object detection due to the barrier principle
- Manipulation-proof, simple teach-in via qTeach or line teach
- IO-Link for extended parameterization options and additional dia-
- Quick mounting by means of M3 threaded bushes made of stainless steel



Picture similar







Technical data			
General data		Electrical data	
Туре	Through beam sensor	Output current	< 50 mA
Emitter / receiver	Receiver	Short circuit protection	Yes
Light source	Use with pulsed red LED	Reverse polarity protection	Yes
Actual range Sb	5 m	Communication interface	
Nominal range Sn	6 m	Baud rate	230,4 kBaud (COM 3)
Smallest object recogniz- able typ.	5 mm (0,5 mm with aperture)	Adjustable parameters	Switching point Time filters LED status indicators Output logic Counter Deactivate the sensor element Find Me function Teach-in mode
Alignment / soiled lens indicator	Flashing output indicator		
Output indicator	LED yellow		
Power on indication	LED green		
Sensitivity adjustment	Teach-in and IO-Link		
Suppression of reciprocal	Yes	IO-Link port type	Class A
influence		Process data length	32 Bit
Electrical data		Process data structure	Bit 0 = SSC1 (presence)
Response time / release time	< 0,5 ms		Bit 2 = quality Bit 3 = alarm
Jitter	< 0,15 ms		Bit 5 = SSC4 (counter)
Voltage supply range +Vs	10 30 VDC		Bit 16-31 = 16 Bit measurement
Current consumption max.	20 mA (@ 10 VDC)	Interface	IO-Link V1.1
(no load)		Additional data	Signal strength
Current consumption typ.	16 mA (@ 24 VDC)		Excess gain Operating cycles
Voltage drop Vd	< 2 VDC		Device temperature
Output function	Light / dark operate	Cycle time	≥ 0,6 ms
Output circuit	Push-pull		

O200.ER-GW1J.72CV/E026_H006


Through beam sensors - miniature

Article number: 11230904


Technical data		
Mechanical data		
Width / diameter	8 mm	
Height / length	25,1 mm	
Depth	14,1 mm	
Туре	Rectangular	
Mechanical mounting	Threaded sleeves M3 (stainless steel)	
Housing material	Plastic (ASA, PMMA)	

Mechanical data	
Front (optics)	PMMA
Connection types	Cable 4 pin, 2 m
Cable characteristics	PVC / PVC 4 x 0,08 mm ²
Ambient conditions	
Operating temperature	-25 +50 °C
Protection class	IP 67

Dimension drawing



Connection diagram



Excess gain curve

