

**Overview**

- 1,6 mm
- NPN make function (NO)
- flylead connector M8
- -25 ... 75 °C
- IP 67





Picture similar



**Technical data**


General data		Mechanical data	
Mounting type	Flush	Housing length	20 mm
Nominal sensing distance Sn	1.6 mm	Connection types	Flylead connector M8
Hysteresis	2 ... 20 % of Sr	Ambient conditions	
Output indicator	LED red	Operating temperature	-25 ... +75 °C
Electrical data		Protection class	IP 67
Switching frequency	3 kHz	Cable	
Voltage supply range +Vs	6 ... 30 VDC	Head A: Connection	M8
Current consumption max. (no load)	12 mA	Head A: Gender	Male
Output circuit	NPN make function (NO)	Head A: Angle cable outlet	0°
Voltage drop Vd	< 2 VDC	Head A: Coding	A
Output current	< 100 mA	Head A: No. of poles	3
Short circuit protection	Yes	Head A: Degree of protection	IP65, IP66K, IP67
Reverse polarity protection	Yes	Cable length	200 mm
Mechanical data		Length tolerance	+ 10 % - 0 %
Type	Cylindrical smooth	Shielded	No
Material (sensing face)	LCP	External sheath: Material	PUR
Housing material	Stainless steel	Cable diameter	2.8 mm
Dimension	4 mm	AWG	28
		Wire cross section	0.09 mm <sup>2</sup>

**Dimension drawing**



- Standard cable length 200 mm (L)

**Dimensions connector**



**Connection diagram**

